

# Product datasheet

Specifications



## Switched Socket, Vivace, Universal, 13A, 250V, 1 gang, 3 pin, white

KB113LS\_WE

### Main

Range	Vivace
Product Or Component Type	Switched socket
Device Short Name	KB113
Device Application	Power supply Control
Device Presentation	Complete product
Switch Application	On/off switching
Main Colour Tint	White
Colour Tint	White

### Complementary

Pilot Light	Red neon indicator
Outlet Poles Configuration	2P + E
Number Of Gangs	1 gang
Colour Tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting Depth	8 mm
Device Mounting	Flush
Mounting Support	Wall mounted
Fixing Mode	By screw M3.5
Fixing Center	60.3 mm
Embedding Depth	22.0 mm
Rated Current	13 A at 250 V AC, no inductive load
Network Frequency	50/60 Hz
Contacts Material	Brass and phosphor bronze
Connections - Terminals	Pillar terminal
Terminal Identifier	L Earth N
Tightening Torque	0.4 N.m
Clamping Connection Capacity	3 x 2.5 mm <sup>2</sup> 2 x 4 mm <sup>2</sup>

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	86 mm
Height	86 mm
Depth	35 mm

## Environment

Standards	IEC 60884
Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	-5...60 °C
Relative Humidity	0...95 %
Operating Altitude	<= 2000 m
Environmental Characteristic	Indoor use
Ip Degree Of Protection	IP20

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	3.5 cm
Package 1 Length	8.6 cm
Package 1 Weight	117.7 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	1.247 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	12020 g

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations