Product datasheet

Specifications





Airing grille cut-out diameter 19mm IP45

NSYCAG19LP

Main

Range	ClimaSys
Product	ClimaSys CA
Range Compatibility	Thalassa Thalassa PLS Thalassa Thalassa PLM Thalassa Thalassa TBS
Product Or Component Type	Plastic ventilation louvre
Accessory / Separate Part Category	Thermal management accessory
Accessory / Separate Part Destination	ClimaSys ventilation system
Mounting Position	Vertical
Fixing Mode	By screws
Device Composition	2 plastic louvre

Complementary

Material	Polyamide 6
Colour	Grey (RAL 7035)
Cut-Out Dimensions	19 mm
Height	External: 30 mm
Width	External: 23.5 mm
Depth	External : 22 mm
Ip Degree Of Protection	IP45

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.0 cm
Package 1 Width	11.5 cm
Package 1 Length	2.5 cm
Package 1 Weight	7.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	300
Package 2 Height	19.0 cm
Package 2 Width	24.0 cm

Package 2 Length	35.0 cm
Package 2 Weight	2.1 kg

Contractual warranty

Warranty

18 months

17 May 2024

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations