Product datasheet

Specification





Switched Socket, Vivace, 13A, 250V, 2 gang, white

KB25_WE_G2

Main

Range	Vivace	
Product Or Component Type	Switched socket	
Device Short Name	KB25	
Device Application	Power supply Control	
Device Presentation	Complete product	
Switch Application	On/off switching	
Main Colour Tint	White	
Colour Tint	White	

Complementary

Outlet Poles Configuration	2P + E
Number Of Gangs	2 gangs
Colour Tint	White
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting Depth	8 mm
Device Mounting	Flush
Mounting Support	Wall mounted
Fixing Mode	By screw M3.5
Fixing Center	120.6 mm
Embedding Depth	22.0 mm
Rated Current	13 A at 250 V AC, resistive
Network Frequency	50/60 Hz
Contacts Material	Brass and phosphor bronze
Connections - Terminals	Pillar terminal
Terminal Identifier	Earth L N
Tightening Torque	0.4 N.m
Clamping Connection Capacity	3 x 2.5 mm ² 2 x 4 mm ²
Width	147 mm

Height	87 mm
Depth	35 mm

Environment

Standards	MS 589 BS 1362-2 SS 145
Ambient Air Temperature For Operation	040 °C
Ambient Air Temperature For Storage	-560 °C
Relative Humidity	095 %
Operating Altitude	<= 2000 m
Environmental Characteristic	Indoor use
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.1 cm
Package 1 Width	8.6 cm
Package 1 Length	14.6 cm
Package 1 Weight	148 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	738 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	50
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	8.4 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations