

Product datasheet

Specifications



TeSys Deca thermal overload relays - remote electrical stop - 48V DC/AC

LAD703E

Main

Range	TeSys
Product Or Component Type	Electrical remote stop
Device Short Name	LAD
Accessory / Separate Part Category	Electrical accessory
Product Compatibility	LR3D01...D35 LRD313...LRD365 LR3D313...LR3D365 LRD01...35
[Uc] Control Circuit Voltage	48 V AC 50/60 Hz 48 V DC

Complementary

Maximum Inrush Power In Va	100 VA
Inrush Power In W	0...100 W
Net Weight	0.09 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.7 cm
Package 1 Width	4.8 cm
Package 1 Length	5.1 cm
Package 1 Weight	107.0 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	32
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.673 kg

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins