# **Product datasheet**

Specification





## Isolated analog converter, Harmony Analog, 0…10V or 4...20mA to 0…10V or 4...20mA

RMCN22BD

### Main

Range Of Product	Harmony Analog	
Product Or Component Type	Voltage/current converter	
Analogue Input Type	Current 420 mA Voltage 010 V DC	
Analogue Output Type	Current 420 mA <= 500 Ohm by cabling Voltage 010 V >= 100 kOhm by cabling	

## Complementary

Protection Type	Short-circuit protection on output
	Overvoltage protection on output (+/- 30 V)
	Reverse polarity protection on output
Abnormal Analogue Output Voltage	-150 V no input or input wire broken
Abnormal Analogue Output Current	430 mA no input or input wire broken
[Us] Rated Supply Voltage	24 V DC +/- 20 %, non isolated
Current Consumption	<= 40 mA for voltage output <= 60 mA for current output
Local Signalling	LED (green) for power ON
Measurement Error	+/- 5 % of full scale at 20 °C (temporary performance degradation when subject to electromagnetic interference)
Repeat Accuracy	+/- 0.2 % full scale at 20 °C +/- 0.6 % full scale at 60 °C
Temperature Coefficient	200 ppm/°C
Clamping Connection Capacity	1 x 2.5 mm <sup>2</sup> 2 x 1.5 mm <sup>2</sup>
Tightening Torque	0.61.1 N.m
Marking	CE
Surge Withstand	0.5 kV during 1.2/50 μs conforming to IEC 61000-4-5
[Ui] Rated Insulation Voltage	2 kV
Fixing Mode	By screws (mounting plate) Clip-on (35 mm symmetrical DIN rail)
Safety Reliability Data	MTTFd = 73.2 years B10d = 67582
Net Weight	0.12 kg

#### **Environment**

Standards	IEC 60584-1
	IEC 60947-1

Product Certifications	GL CSA UL	
Ip Degree Of Protection	IP20 (terminal block) IP50 (housing)	
Fire Resistance	850 °C conforming to IEC 60695-2-1 850 °C conforming to UL	
Shock Resistance	50 gn for 11 ms conforming to IEC 60068-2-27	
Vibration Resistance	5 gn (f= 10100 Hz) conforming to IEC 60068-2-6	
Resistance To Electrostatic Discharge	6 kV (in contact) conforming to IEC 61000-4-2 level 3 8 kV (in air) conforming to IEC 61000-4-2 level 3	
Resistance To Fast Transients	1 kV (on input-output) conforming to IEC 61000-4-4 2 kV (on power supply) conforming to IEC 61000-4-4	
Disturbance Radiated/Conducted	CISPR 22 group 1 - class B CISPR 11	
Ambient Air Temperature For Storage	-4085 °C	
Ambient Air Temperature For Operation	050 °C mounting side by side 060 °C 2 cm spacing	
Pollution Degree	2 conforming to IEC 60664-1	

## **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.7 cm
Package 1 Width	8.2 cm
Package 1 Length	8.5 cm
Package 1 Weight	103.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	47
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	5.62 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information


## **Product datasheet**

### RMCN22BD

**Dimensions Drawings** 

## Analog Interface (Converter)

#### **Dimensions**



(1) Terminal block AB1TP435U or AB1RRNTP435U2


## **Product datasheet**

### RMCN22BD


Mounting and Clearance

#### Mounting

#### Mounting on Rails AM1 \*\*\*\*\*



#### **Panel Mounting**




#### RMCN22BD

Connections and Schema


#### Analog Interface: Voltage/Current Converter

#### Wiring Diagrams

**Current input signal** 



#### Voltage input signal



The input, output and power supply lines must be kept away from the power cables to avoid effects due to induced interference.

The supply, input and output cables must be shielded as indicated in the schemes and must be kept away from each other