



# module TM3 - 4 analog inputs

TM3AI4

# Main

Range Of Product	Modicon TM3  Analog input module	
Product Or Component Type		
Range Compatibility	Modicon M221	
	Modicon M241	
	Modicon M251	
	Modicon M262	
Analogue Input Number	4	
Analogue Input Type	current 420 mA	
· , ,,	current 020 mA	
	voltage 010 V	
	voltage - 1010 V	

# Complementary

Analogue Input Resolution	12 bits 11 bits + sign	
Permissible Continuous Overload	13 V, analogue input type: voltage 40 mA, analogue input type: current	
Input Impedance	<= 50 Ohm current >= 1 MOhm voltage	
Lsb Value	2.44 mV 010 Vvoltage 4.88 mV - 1010 Vvoltage 4.88 μA 020 mAcurrent 3.91 μA 420 mAcurrent	
Conversion Time	1 ms + 1 ms per channel + 1 controller cycle time	
Sampling Duration	1 ms	
Absolute Accuracy Error	+/- 0.1 % of full scale at 25 °C +/- 1 % of full scale	
Temperature Drift	+/- 0.006 %FS/°C	
Repeat Accuracy	+/-0.5 %FS	
Non-Linearity	+/- 0.2 %FS	
Cross Talk	<= 1 LSB	
[Us] Rated Supply Voltage	24 V DC	
Supply Voltage Limits	20.428.8 V	
Type Of Cable	Twisted shielded pairs cable <30 m for input circuit	
<b>Current Consumption</b>	Consumption 35 mA at 5 V DC via bus connector no load 45 mA at 5 V DC via bus connector full load 30 mA at 24 V DC via external supply	
Local Signalling	1 LED (green) for PWR	

<u> </u>		
Electrical Connection	10 x 1.5 mm² removable screw terminal block with pitch 3.81 mm adjustment for	
	inputs and supply	
	10 x 1.5 mm² removable screw terminal block with pitch 3.81 mm adjustment for	
	inputs	
Insulation	Between input and supply at 1500 V AC	
	Between input and internal logic at 500 V AC	
Marking CE		
Surge Withstand	1 kV power supply common mode conforming to IEC 61000-4-5	
	0.5 kV power supply differential mode conforming to IEC 61000-4-5	
	1 kV input common mode conforming to IEC 61000-4-5	
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715	
	Top hat type TH35-7.5 rail conforming to IEC 60715	
	plate or panel with fixing kit	
Height	90 mm	
Depth	70 mm	
Width	23.6 mm	
Net Weight	0.11 kg	

# **Environment**

Standards	IEC 61131-2	
Product Certifications	CE UKCA RCM EAC cULus cULus HazLoc	
Resistance To Electrostatic Discharge	8 kV in air conforming to IEC 61000-4-2 4 kV on contact conforming to IEC 61000-4-2	
Resistance To Electromagnetic Fields	10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3 3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3 1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3	
Resistance To Magnetic Fields 30 A/m conforming to IEC 61000-4-8		
Resistance To Fast Transients	ansients 1 kV (I/O) conforming to IEC 61000-4-4	
Resistance To Conducted Disturbances	10 V 0.1580 MHz conforming to IEC 61000-4-6 3 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to Marine specification (LR, ABS, DNV, GL)	
Electromagnetic Emission	Radiated emissions - test level: 40 dBμV/m QP class A ( 10 m) at 30230 MHz conforming to IEC 55011 Radiated emissions - test level: 47 dBμV/m QP class A ( 10 m) at 2301000 MHz conforming to IEC 55011	
Immunity To Microbreaks	10 ms	
Ambient Air Temperature For Operation	-1055 °C horizontal installation -1035 °C vertical installation	
Ambient Air Temperature For Storage	-2570 °C	
Relative Humidity	1095 %, without condensation (in operation) 1095 %, without condensation (in storage)	
Ip Degree Of Protection	IP20	
Pollution Degree	2	
Operating Altitude	02000 m	
Storage Altitude	03000 m	
Vibration Resistance	3.5 mm at 58.4 Hz on DIN rail 3 gn at 8.4150 Hz on DIN rail	

Shock Resistance

15 gn for 11 ms

# **Packing Units**

PCE
1
7.585 cm
10.598 cm
12.814 cm
210.0 g
S04
42
30 cm
40 cm
60 cm
10.08 kg
P12
504
105 cm
120 cm
80 cm
132 kg



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

# Well-being performance


<b>⊘</b>	Toxic Heavy Metal Free	
	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

# **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

# **Dimensions Drawings**

#### **Dimensions**




(\*) 8.5 mm/0.33 in when the clamp is pulled out.


# **TM3AI4**

# Mounting and Clearance

# **Spacing Requirements**




# Mounting on a Rail



# **Incorrect Mounting**





#### Mounting on a Panel Surface



(1) Install a mounting strip

# **Mounting Hole Layout**






Connections and Schema

# Analogue Input Module

#### Wiring Diagram (Current / Voltage)



- (\*) Type T fuse
- (1) Current/Voltage analog output device