Product datasheet

Specification





Contactor, TeSys Deca, 3P(3NO), AC-3/AC-3e, <=440V, 32A, 220V AC 50/60Hz coil, screw clamp terminals

LC1D32M7

Main

Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-4 AC-1 AC-3 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC
[le] Rated Operational Current	32 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 50 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 32 A (at <60 °C) at <= 440 V AC AC-3e for power circuit
[Uc] Control Circuit Voltage	220 V AC 50/60 Hz

Complementary

•	
Motor Power Kw	7.5 kW at 220230 V AC 50/60 Hz (AC-3)
	15 kW at 380400 V AC 50/60 Hz (AC-3)
	15 kW at 415440 V AC 50/60 Hz (AC-3)
	18.5 kW at 500 V AC 50/60 Hz (AC-3)
	18.5 kW at 660690 V AC 50/60 Hz (AC-3)
	7.5 kW at 400 V AC 50/60 Hz (AC-4)
	7.5 kW at 220230 V AC 50/60 Hz (AC-3e)
	15 kW at 380400 V AC 50/60 Hz (AC-3e)
	15 kW at 415440 V AC 50/60 Hz (AC-3e)
	18.5 kW at 500 V AC 50/60 Hz (AC-3e)
	18.5 kW at 660690 V AC 50/60 Hz (AC-3e)
Motor Power Hp	2 hp at 115 V AC 50/60 Hz for 1 phase motors
	5 hp at 230/240 V AC 50/60 Hz for 1 phase motors
	10 hp at 200/208 V AC 50/60 Hz for 3 phases motors
	10 hp at 230/240 V AC 50/60 Hz for 3 phases motors
	20 hp at 460/480 V AC 50/60 Hz for 3 phases motors
	25 hp at 575/600 V AC 50/60 Hz for 3 phases motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With
[Ith] Conventional Free Air	10 A (at 60 °C) for signalling circuit
Thermal Current	50 A (at 60 °C) for power circuit
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1
	250 A DC for signalling circuit conforming to IEC 60947-5-1
	550 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	550 A at 440 V for power circuit conforming to IEC 60947

[Icw] Rated Short-Time Withstand	260 A 40 °C - 10 s for power circuit
Current	430 A 40 °C - 1 s for power circuit
	60 A 40 °C - 10 min for power circuit
	138 A 40 °C - 1 min for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
ū	63 A gG at <= 690 V coordination type 1 for power circuit
	63 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2 mOhm - Ith 50 A 50 Hz for power circuit
Power Dissipation Per Pole	2 W AC-3
	5 W AC-1
	2 W AC-3e
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1
	Power circuit: 600 V CSA certified
	Power circuit: 600 V UL certified
	Signalling circuit: 690 V conforming to IEC 60947-1
	Signalling circuit: 600 V CSA certified
	Signalling circuit: 600 V UL certified
Overvoltage Category	Ш
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1
	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO
	13849-1
Mechanical Durability	15 Mcycles
Electrical Durability	1.65 Mcycles 32 A AC-3 at Ue <= 440 V
· · · · · · · · · · · · · · · · · · ·	1.4 Mcycles 50 A AC-1 at Ue <= 440 V
	1.65 Mcycles 32 A AC-3e at Ue <= 440 V
Control Circuit Type	AC at 50/60 Hz standard
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz
_	0.81.1 Uc (-4060 °C):operational AC 50 Hz
	0.851.1 Uc (-4060 °C):operational AC 60 Hz
	11.1 Uc (6070 °C):operational AC 50/60 Hz
Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 20 °C)
	70 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 20 °C)
	7.5 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	23 W at 50/60 Hz
Operating Time	1222 ms closing
Operating Time	1222 ms closing 419 ms opening
Operating Time Maximum Operating Rate	· · · · · · · · · · · · · · · · · · ·

> 10 MOhm for signalling circuit 1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact	
type mirror contact 1 NC conforming to IEC 60947-4-1 25400 Hz	
1 NO + 1 NC type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1	
er Philips No 2 ver pozidriv No 2 er pozidriv No 2	
ver flat Ø 6 mm ver Philips No 2 er flat Ø 6 mm	
ss: solid without	
s: flexible with	
ss: flexible without	
ss: flexible without	
: solid without	
ss: flexible with	
: flexible with cable	
: flexible without	
:	

Climatic Withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat	
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating	
Operating Altitude	03000 m	
Fire Resistance	850 °C conforming to IEC 60695-2-1	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor closed (15 Gn for 11 ms) Shocks contactor open (8 Gn for 11 ms)	
Height	85 mm	
Width	45 mm	
Depth	92 mm	
Net Weight	0.375 kg	

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	9.200 cm
Package 1 Length	11.200 cm
Package 1 Weight	412.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.502 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	160
Package 3 Height	45.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	76.016 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Pvc Free


Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	

LC1D32M7

Dimensions Drawings

Dimensions



- (1) Including LAD 4BB
- (2) Minimum electrical clearance

LC1		D25D38 (3-pole)
b	without add-on blocks	85
b1	with LAD 4BB	98
	with LA4 D●2	114 ⁽¹⁾
	with LA4 DF, DT	123 ⁽¹⁾
	with LA4 DW, DL	130(1)
С	without cover or add-on blocks	90
	with cover, without add-on blocks	92
c1	with LAD N or C (2 or 4 contacts)	123
c2	with LA6 DK10, LAD 6K10	135
сЗ	with LAD T, R, S	143
	with LAD T, R, S and sealing cover	147
(1)	Including LAD 4BB.	

Connections and Schema

Wiring

