Product datasheet

Specification





analogue input cartridge, Modicon M241, 2 temperature inputs

TMC4TI2

Main

Range Of Product	Madian MO44	
	Modicon M241	
Product Or Component Type	Analogue input cartridge	
Product Compatibility	Modicon M241C	
Analogue Input Number	2	

Complementary

Complementary		
Analogue Input Type	thermocouple - 2001000 °C with thermocouple J	
	thermocouple - 2001300 °C with thermocouple K	
	thermocouple 01760 °C with thermocouple R	
	thermocouple 01760 °C with thermocouple S	
	thermocouple 01820 °C with thermocouple B	
	thermocouple - 200400 °C with thermocouple T	
	·	
	thermocouple - 2001300 °C with thermocouple N	
	thermocouple - 200800 °C with thermocouple E	
	Ni 100/Ni 1000 temperature probe - 60180 °C	
	Pt 100 temperature probe - 200850 °C	
	Pt 1000 temperature probe - 200600 °C	
Analogue Input Resolution	cion 14 bits	
Lsb Value	0.1 °C	
Sampling Duration	100 ms	
Absolute Accuracy Error	+/- 0.5 % of full scale at 25 °C for Pt 100/Pt 1000, Ni 100/ Ni 1000 temperature probe	
-	+/- 0.2 % of full scale at 25 °C for thermocouple K - 2001300 °C	
	+/- 0.2 % of full scale at 25 °C for thermocouple J - 2001000 °C	
	+/- 0.2 % of full scale at 25 °C for thermocouple E - 200800 °C	
	•	
	+/- 0.2 % of full scale at 25 °C for thermocouple T - 200400 °C	
	+/- 0.2 % of full scale at 25 °C for thermocouple N - 2001300 °C	
	+/- 0.2 % of full scale at 25 °C for thermocouple B 250400 °C	
	+/- 0.1 % of full scale at 25 °C for thermocouple B 4001280 °C	
	+/- 0.2 % of full scale at 25 °C for thermocouple R, S 01760°C	
Temperature Drift	+/- 0.008 %FS/°C	
Repeat Accuracy	+/- 0.1 %FS	
Non-Linearity	+/- 0.05 %FS	
Cross Talk	80 dB	
Type Of Cable	Twisted shielded pairs cable	
Electrical Connection	1 x 1.5 mm² 1 spring terminal block with pitch 3.81 mm adjustment for outputs and	
	supply	
Maximum Cable Distance Between Devices	Twisted shielded pairs cable: <30 m for input	
Insulation	Between input and internal logic at 500 V DC	
	Non-insulated between inputs	
Supply Voltage Limits	20.428.8 V	
Local Signalling 1 LED (green) for PWR		

Height	50 mm	
Depth	21 mm	
Width	34 mm	
Net Weight	0.055 kg	
Permissible Continuous Overload	6 V	
Input Impedance	>= 1 MOhm	

Environment

Immunity To Microbreaks 10 ms

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	3.0 cm
Package 1 Length	3.5 cm
Package 1 Weight	74.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	50
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.164 kg



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
⊘	Rohs Exemption Information	Yes
	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information