Product datasheet

Specification





Enclosed DOL starter, TeSys LE, 3.7-5.5A, 24V AC coil, including 1 LC1K, LR2K, 2 pushbuttons, yellow indicator

LE1M35B712

Main

Range	TeSys	
Product Name	TeSys LE	
Device Short Name	LE1M	
Product Or Component Type	Enclosed DOL starter	
evice Application Standard		
Utilisation Category	AC-3	
Device Composition	Contactor Earth terminal Neutral terminal Thermal overload relay	
Thermal Protection Adjustment Range	3.75.5 A	
Motor Power Kw	0.75 kW at 240 V AC 50/60 Hz 2.2 kW at 415 V AC 50/60 Hz 1.1 kW at 220/230 V AC 50/60 Hz 2.2 kW at 380/400 V AC 50/60 Hz	
[Uc] Control Circuit Voltage	24 V AC 50/60 Hz	
Control Type	Push-button start green I Push-button stop/reset red O	

Complementary

Local Signalling	Operating: LED (yellow)	
Cable Entry Number	2 ISO20 top	
	2 ISO25 top	
	2 Pg 13 top	
	2 Pg 21 top	
	2 ISO20 bottom	
	2 ISO25 bottom	
	2 Pg 13 bottom	
	2 Pg 21 bottom	
	2 Pg 16 top	
	2 Pg 16 bottom	
Width	78 mm	
Height	160 mm	
Depth	108 mm	
Net Weight	Weight 0.6 kg	

Environment

Material	ABS (acrylonitrile butadiene-styrene)
Ip Degree Of Protection	IP65 conforming to IEC 60529

Standards	IEC 60947-4-1
Ambient Air Temperature For Operation	-540 °C
Environmental Characteristic	Standard environment
Product Certifications	LIKCA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	16.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	571.0 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information