Product datasheet

Specification





Switch disconnector, TeSys Control, for ON/emergency stop, 63A,4 screws fixing, for mounting on door

VCF3

Main

Range	TeSys
Product Name	TeSys VARIO
Device Short Name	VCF
Product Type	Emergency stop switch disconnector

Complementary

Complementary	
Device Composition	Switch Handle
Mounting Support	Handle: door Switch: door
Mounting Method	By 4 screws for handle
Performance Level	High performance
Number Of Poles	3P
Contact Type And Composition	3 NO
[Ue] lec Rated Operational Voltage	690 V AC 50/60 Hz
lec Rated Operational Power In W	11 kW at 230240 V (AC-3) 22 kW at 500 V (AC-3) 22 kW at 690 V (AC-23A) 30 kW at 500 V (AC-23A) 18.5 kW at 400415 V (AC-3) 18.5 kW at 690 V (AC-3) 15 kW at 230240 V (AC-23A) 22 kW at 400415 V (AC-23A)
[le] Rated Operational Current	41.5 A AC-23 Ue: 400 V
[Ith] Conventional Free Air Thermal Current	63 A
[Ithe] Conventional Enclosed Thermal Current	50 A
Making Capacity (I Rms)	630 A at 400 V AC-21A 630 A at 400 V AC-22A 630 A at 400 V AC-23A
Breaking Capacity	500 A at 400 V (AC-21A) 500 A at 400 V (AC-22A) 500 A at 400 V (AC-23A)
Rated Conditional Short Circuit Current	10 kA at 400 V - associated fuse 63 A aM 10 kA at 400 V - associated fuse 63 A gG
[Icm] Rated Short Circuit Making Capacity	2.1 kA at 400 V at Ipeak
[Icw] Rated Short Time Withstand Current	756 A at 400 V duration: 1 s
[Uimp] Rated Impulse Withstand Voltage	8 kV

Suitability For Isolation	Yes	
Network Type	DC AC	
Intermittent Duty Class	30	
Control Type	Rotary handle	
Rotary Handle Mounting Style	Direct	
Handle Color	Red	
Handle Front Plate Color	Yellow	
Rotary Handle Padlocking	1 to 3 padlocks 48 mm	
Marking	0 - 1	
Mechanical Durability	30000 cycles	
Electrical Durability	30000 cycles AC-21 30000 cycles DC-15	
lec Terminal Connection	Power circuit: screw clamp terminals25 mm² - solid Power circuit: screw clamp terminals16 mm² - flexible - with cable end	
Tightening Torque	Power circuit: 4 N.m - on screw clamp terminals	
Base Dimension	60 x 60 mm	
Height	83 mm	
Width	60 mm	
Product Weight	0.56 kg	

Environment

Standards	IEC 60947-3
Product Certifications	GL CCC CSA UL UKCA
Degree Of Protection	IP20 conforming to IEC 60529 IP65
Protective Treatment	тс
Mechanical Robustness	Vibrations 10150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27
Ambient Air Temperature For Operation	-2050 °C
Fire Resistance	960 °C conforming to IEC 60695-2-1
Compatibility Code	Main switch disconnector

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.800 cm
Package 1 Width	8.500 cm
Package 1 Length	11.800 cm
Package 1 Weight	349.000 g
Unit Type Of Package 2	S02

Number Of Units In Package 2	12
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.422 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	192
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	81.060 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
Ø	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations