Product datasheet





EasyPact CVS630N circuit breaker, 50 kA at 415 VAC, 3P 3d, TM-D 500 A trip unit

LV563315

Main

Range	EasyPact
Range Of Product	EasyPact CVS400630
Product Name	EasyPact CVS
Device Short Name	CVS630N
Product Or Component Type	Circuit breaker
Device Application	Distribution
Poles Description	3P
Protected Poles Description	3D
Earth Leakage Protection (Vigi Add On)	Without
[In] Rated Current	500 A at 40 °C
Network Type	AC
Utilisation Category	Category A
[Icu] Breaking Capacity	70 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 50 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 42 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2
Trip Unit Name	TM-D
Trip Unit Technology	Thermal-magnetic
Trip Unit Rating	500 A at 40 °C
Protection Type	Overload protection (thermal) Short-circuit protection (magnetic)

Complementary

•							
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to EN/IEC 60947-2						
Network Frequency	50/60 Hz						
Breaking Capacity Code	N						
[Ics] Rated Service Breaking Capacity	70 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 50 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 32 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2						
Mechanical Durability	15000 cycles						
Electrical Durability	4000 cycles 415 V In conforming to IEC 60947-2						
Control Type	Toggle						
Thermal Protection Adjustment Range	350500 A						
Long Time Pick-Up Adjustment Type Ir	Adjustable						

Life Is On Schneider 13 May 2024



Long Time Pick-Up Adjustment Range	0.71 x ln
Long Time Delay Adjustment Type	Fixed
Instantaneous Pick-Up Adjustment Type Ii	Adjustable
Instantaneous Pick-Up Adjustment Range	510 x In
Contact Position Indicator	Yes
Mounting Support	Backplate
Mounting Mode	Fixed
Upside Connection	Front
Downside Connection	Front
Connections - Terminals	Screw connection
Connection Pitch	45 mm
Compatibility Code	CVS630
Width	140 mm
Depth	110 mm
Height	255 mm
Net Weight	5.2 kg

Environment

Standards	IEC 60947-2 EN 60947-2
Product Certifications	GOST IEC
Electrical Shock Protection Class	Class II
Pollution Degree	3 conforming to IEC 60664-1
Ip Degree Of Protection	IP40
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24.4 cm
Package 1 Width	16.0 cm
Package 1 Length	30.0 cm
Package 1 Weight	5.38 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	2
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	10.76 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh


Well-being performance

②	Mercury Free	
	Rohs Exemption Information	Yes
	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information


Dimensions Drawings





Туре	Α	A1	A2	A3	A4	A5	A6	A7	A8	A9	В	B1	B2	C1	C2	C3	E1
CV8100160/250	66.5	161	64	146	179.5	155.5	226	169	226	250.5	52.5	105	140	81	66	111	62.5
C245/4000930	127,5	255	142,5	200	297	227.5	3.55	242.5	3.00	337	700	140	188	95.5	110	168	100
Type	E2	E3	E4	E5	E6	E7	E8	F1	F2	F3	G1	G2	G3	G4	G5	ØT	U
CVB100M60/250	125	FE	140	137.5	200	145	215	216	17.5	70	56	78	13.5	25	17.5	24	y 32
CV5401481	200	113.5	223	200	200	2135	327	45	22.5	90	-	00	-	-		32	y 35


[8] C3-126mm for EasyPost CVS2509JF.

Assembly










Туре	Α	A1	A2	A3	A4	A5	A6	A7	A8	A9	В	B1	B2	C1	C2	C3	E1
CV8100160/250	66.5	161	64	146	179.5	155.5	236	169	226	250.5	52.5	105	146	81	66	191@	62.5
C2V52400/930	127.5	286	142,5	200	297	227.6	3.55	242.5	300	337	70	140	188	95.5	110	168	100
Type	E2	E3	E4	E5	E6	E7	EB	F1	F2	F3	G1	G2	G3	G4	G5	ØT	U
CW9100M60/250	125	FE	140	137.5	200	145	215	216	17.5	70	SB	78	13.5	25	17.5	24	y 32
CVS400/630	200	113.5	223	200	200	2135	327	45	22.5	90	-			-		32	y 35

(2) C3=126mm for EasyPast CVS2500/F.

Performance Curves



Reflex tripping.