Product datasheet

Specifications





Additional neutral block,TeSys Control,40A,for V02-V2

VZ11

Main

Range	TeSys
Device Short Name	VZ
Product Or Component Type	Additional neutral block
Performance Level	High performance
Poles Description	1N
Contacts Type And Composition	1 NO
Contact Operation	Early make, late break
Product Compatibility	V1 V2 V02 V0 V01
Range Compatibility	TeSys TeSys VARIO switch disconnector
Network Type	AC DC
Network Frequency	50/60 Hz

Complementary

Mounting Location	Left Right
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	6 kV
[Ith] Conventional Free Air Thermal Current	40 A
Mechanical Durability	100000 cycles
Electrical Durability	30000 cycles DC-15 100000 cycles AC-21
Connections - Terminals	Screw clamp terminals6 mm² - flexible - with cable end Screw clamp terminals10 mm² - solid
Tightening Torque	2.1 N.m - on screw clamp terminals
Height	74 mm
Width	16 mm
Depth	35 mm
Net Weight	0.05 kg

Environment



Standards	IEC 60947-3	
Product Certifications	GL	
	CSA	
	UL	
	UKCA	
Protective Treatment	TC	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Mechanical Robustness	Vibrations 10150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (15 gn) conforming to IEC 60068-2-27	
	Shocks 11 his (15 gh) comorning to IEC 60000-2-21	
Ambient Air Temperature For Operation	-2050 °C	
Fire Resistance	960 °C conforming to IEC 60695-2-1	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.7 cm
Package 1 Width	5.5 cm
Package 1 Length	9.0 cm
Package 1 Weight	48.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	69
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.582 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Toxic Heavy Metal Free
⊘	Mercury Free
Ø	Rohs Exemption Information Yes
	Pvc Free
Ø	Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations