Product datasheet

Specifications





Circuit breaker, EasyPact MVS, 3 Poles, 3200A, 65kA, EDO, ET6, drawout, electrical

MVS32H3NW6L

Main

Range	EasyPact						
Product Name	MVS32H						
Device Short Name	MVS32H						
Product Or Component Type	Circuit breaker						
Device Application	Distribution						
Poles Description	3P						
Protected Poles Description	3P 3d						
[In] Rated Current	3200 A at 40 °C						
Network Type	AC						
[Ue] Rated Operational Voltage	390 V AC 50/60 Hz conforming to IEC 60947-2						
Breaking Capacity Code	н						
Suitability For Isolation	Yes conforming to IEC 60947-2						
Utilisation Category	Category B						
Trip Unit Name	ET6G						
Trip Unit Technology	Electronic						
Trip Unit Rating	3200 A						

Complementary

Network Frequency	50/60 Hz
Control Type	Electrically operated
Mounting Mode	Drawout
Mounting Support	Rail Base plate
Connection Position	Horizontal Vertical
Location Of Connection	Rear
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	12 kV conforming to IEC 60947-2
Circuit Breaker Ct Rating	3200 A
Breaking Capacity	65 kA Icu at 220440 V AC 50/60 Hz conforming to IEC 60947-2
[Ics] Rated Service Breaking Capacity	65 kA (Ics) at 220440 V AC 50/60 Hz conforming to IEC 60947-2 50 kA (Ics) at 690 V AC 50/60 Hz conforming to IEC 60947-2

Mechanical Durability	20000 cycles (with maintenance) conforming to IEC 60947-2
	10000 cycles (without maintenance) conforming to IEC 60947-2
Electrical Durability	Category B: 5000 cycles 440 V AC 50/60 Hz without maintenance conforming to IEC 60947-2
	Category B: 2500 cycles 690 V AC 50/60 Hz without maintenance conforming to IEC
	60947-2
Connection Pitch	115 mm without spreader
Contact Position Indicator	Yes
[Icm] Rated Short-Circuit Making Capacity	143 kA (Icm) at 220440 V AC 50/60 Hz conforming to IEC 60947-2
[Icw] Rated Short-Time Withstand	65 kA (1 s) at 220440 V AC 50/60 Hz conforming to IEC 60947-2
Current	50 kA (1 s) at 690 V AC 50/60 Hz conforming to IEC 60947-2
	50 kA (3 s) at 440/690 V AC 50/60 Hz conforming to IEC 60947-2
Trip Unit Protection Functions	LSIG
Protection Type	Instantaneous short-circuit protection
	Short time short-circuit protection Overload protection (long time)
	Earth fault
Fault Indication	Earth fault
	Overload
	Internal fault Short-circuit
Long Time Pick-Up Adjustment	Adjustable 9 settings
Type Ir	Aujustable 9 settings
Long Time Pick-Up Adjustment Range	0.41 x ln
Long Time Delay Adjustment Type	Adjustable 9 settings
[Tr] Long-Time Delay Adjustment Range	0.524 s at 6 x lr
Short-Time Pick-Up Adjustment Type Isd	Adjustable 9 settings
[Isd] Short-Time Pick-Up Adjustment Range	1.510 x lr
Short-Time Delay Adjustment Type	Adjustable 5 settings
[Tsd] Short-Time Delay Adjustment Range	100400 ms
Instantaneous Pick-Up Adjustment Type Ii	Adjustable 9 settings
Instantaneous Pick-Up Adjustment Range	Off
	215 x ln
Ground-Fault Pick-Up Adjustment Type	Adjustable 9 settings
Ground-Fault Time Delay Adjustment Type -Tg	Adjustable 5 settings
[Tg] Ground-Fault Time Delay Adjustment Range	100400 ms
[Ig] Ground-Fault Pick-Up Adjustment Range	5001200 A
Zone Selective Interlocking Zsi	With
Current Sensor Rating Range	1000/4000 A
Maximum Breaking Time	25 ms
Maximum Closing Response Time	70 ms
Height	439 mm
Width	441 mm
Depth	395 mm
Net Weight	90 kg

Environment

Standards	IEC 60947-2						
Product Certifications	CCS GOST IEC CCC						
Pollution Degree	conforming to IEC 60664-1						
Ip Degree Of Protection	P40						
Ambient Air Temperature For Operation	-570 °C						
Ambient Air Temperature For Storage	-4085 °C without control unit -2585 °C with control unit						

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	42.0 cm
Package 1 Width	35.0 cm
Package 1 Length	50.0 cm
Package 1 Weight	38.0 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance


Mercury Free
Rohs Exemption Information Yes
Pvc Free


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information


Product datasheet


Dimensions Drawings






Assembly






Performance Curves



1.1	1.4	110
-1	7	л.
- 1		1

lg = ln x	Α	В	С	D	Е	F	G	Н	J
In ≤ 400 A	0.3	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1
400 A < In ≤ 1000 A	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1
In≥1250A	500	640	720	800	880	960	1040	1120	1200



1	A	ъ.
£	J.	J
		r

lg = ln x	Α	В	С	D	E	F	G	Н	J
In ≤ 400 A	0.3	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1
400 A < In ≤ 1000 A	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1
In≥1250A	500	640	720	800	880	960	1040	1120	1200