# **Product datasheet**

Specifications





### ClimaSys forced vent. IP54, 58m3/ h, 24V DC, with outlet grille and filter G2

NSYCVF38M24DPF

#### Main

Range	ClimaSys
Product Name	ClimaSys CV
Product Or Component Type	Fan
Type Of Filter	Standard
Flow Rate	Free flow rate with standard filter: 58 m3/h
[Us] Rated Supply Voltage	1027.6 V
Input Voltage	24 V DC

## Complementary

· · · · · · · · · · · · · · · · · ·	
Absorbed Power	3.6 W
[In] Rated Current	0.18 A
Noise Level < At	4041 dB
Bearing Type	Ball
Height	External: 137 mm
Width	External: 117 mm
Depth	External : 49 mm
Cut-Out Dimensions	92 x 92 mm
Net Weight	0.23 kg
Material	Outlet grille: injected thermoplastic (ASA PC)
Colour	Outlet grille: grey (RAL 7035)
Ambient Air Temperature For Operation	-1070 °C
Ambient Air Temperature For Storage	-4070 °C
Maximum Pressure	29 Pa flow rate 0 m³/h
Connections - Terminals	Cable
Ip Degree Of Protection	IP54
Device Composition	1 axial motor 2 protective grille: on the front and rear surfaces 1 filter: front of axial motor 1 outlet grille: front 1 cut-out template
Condition Of Use	Flow rates depends on the work point, see ProClima software Filter must be cleaned and replaced regularly Overfrequent filter replacement should be avoided Surrounding environment must be relatively clean Outside temperature must be 5 °C lower than inside temperature

### **Packing Units**

U	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	12 cm
Package 1 Length	14.8 cm
Package 1 Weight	282 g
Unit Type Of Package 2	P12
Number Of Units In Package 2	640
Package 2 Height	120 cm
Package 2 Width	80 cm
Package 2 Length	114 cm
Package 2 Weight	199 kg

### **Contractual warranty**

Warranty

18 months

#### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information