



# module XPSAC - Emergency stop - 230 V AC

XPSAC3721P

! Discontinued on: 16 Jan 2024

! Discontinued

### Main

Range Of Product	uct Preventa Safety automation	
Product Or Component Type	Preventa safety module	
Safety Module Name	XPSAC	
Safety Module Application	For emergency stop and switch monitoring	
Function Of Module	Emergency stop Switch monitoring	
Safety Level	Can reach PL e/category 4 conforming to EN/ISO 13849-1 Can reach SILCL 3 conforming to EN/IEC 62061	
Safety Reliability Data	MTTFd = 210.4 years conforming to EN/ISO 13849-1 DC > 99 % conforming to EN/ISO 13849-1 PFHd = 3.56E-9 1/h conforming to EN/IEC 62061	
Type Of Start	Unmonitored	
Connections - Terminals	Captive screw clamp terminals, removable terminal block, 1 x 0.21 x 2.5 mm² flexible with cable end, with double bezel Captive screw clamp terminals, removable terminal block, 1 x 0.21 x 2.5 mm² solid with cable end, with double bezel Captive screw clamp terminals, removable terminal block, 1 x 0.251 x 2.5 mm² flexible with cable end, with double bezel Captive screw clamp terminals, removable terminal block, 2 x 0.22 x 1 mm² solid with cable end, with double bezel Captive screw clamp terminals, removable terminal block, 2 x 0.22 x 1.5 mm² flexible with cable end, with double bezel Captive screw clamp terminals, removable terminal block, 2 x 0.252 x 1 mm² flexible with cable end, with double bezel Captive screw clamp terminals, removable terminal block, 2 x 0.52 x 1.5 mm² flexible with cable end, with double bezel Captive screw clamp terminals, removable terminal block, 2 x 0.52 x 1.5 mm² flexible with cable end, with double bezel	
Output Type	Relay instantaneous opening, 3 NO circuit(s), volt-free	
Number Of Additional Circuits	1 solid state output	
[Us] Rated Supply Voltage	230 V AC - 1510 %	

## **Complementary**

16 May 2024

50/60 Hz	
6 VA AC	
230 V	
180 VA holding AC-15 C300 relay output 1800 VA inrush AC-15 C300 relay output	
1.5 A at 24 V (DC-13) time constant: 50 ms for relay output	
6 A per relay for relay output	
10.5 A	

Associated Fuse Rating	4 A gG or gL for relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200 6 A fast blow for relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200	
Minimum Output Current	nt 10 mA for relay output	
Minimum Output Voltage	16 V for relay output	
Maximum Response Time On Input Open	100 ms	
[Ui] Rated Insulation Voltage	300 V (pollution degree 2) conforming to IEC 60947-5-1 300 V (pollution degree 2) conforming to DIN VDE 0110 part 1	
[Uimp] Rated Impulse Withstand Voltage	4 kV overvoltage category III conforming to IEC 60947-5-1 4 kV overvoltage category III conforming to DIN VDE 0110 part 1	
Local Signalling	2 LEDs	
Current Consumption	25 mA at 230 V AC on power supply	
Mounting Support	35 mm symmetrical DIN rail	
Net Weight	0.21 kg	

## **Environment**

Standards	EN/ISO 13850 EN 60204-1 EN/IEC 60947-5-1 EN 1088/ISO 14119
Product Certifications	CSA UL TÜV
Ip Degree Of Protection	IP20 (terminals) conforming to EN/IEC 60529 IP40 (enclosure) conforming to EN/IEC 60529
Ambient Air Temperature For Operation	-1055 °C
Ambient Air Temperature For Storage	-2585 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.900 cm
Package 1 Width	2.800 cm
Package 1 Length	10.300 cm
Package 1 Weight	245.000 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	16
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.291 kg

# **Contractual warranty**

Warranty	18 months
vvarianty	10 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information