Product datasheet

Specifications





Controller M100 - 20I/12O relay - 220VAC

TM100C32RN

Main

| Range Of Product | Easy Modicon M100 |
|-----------------------------|--|
| Product Or Component Type | Logic controller |
| [Us] Rated Supply Voltage | 100240 V AC |
| Discrete I/O Number | 32 |
| Discrete Input Number | I2I5: 4 fast input I0I1: 2 high speed input I6I19: 14 regular input |
| Discrete Output Number | 12 relay |
| Discrete Input Voltage | 24 V |
| Discrete Input Voltage Type | DC |
| Discrete Input Current | 7 mA for regular input 7 mA for fast input 9 mA for high speed input |
| Discrete Output Voltage | 24 V DC 220 V AC |
| Discrete Output Current | 2 A |
| Discrete Output Type | Relay normally open |
| Power Consumption In Va | 3244 VA at 100240 V AC (with max I/O) |

Complementary

| Supply Voltage Limits | 85264 V |
|----------------------------|---|
| Voltage State 1 Guaranteed | >= 15 V for input |
| Voltage State 0 Guaranteed | <= 5 V for input |
| Network Frequency | 50/60 Hz |
| Inrush Current | 50 A |
| Input Impedance | 3.3 kOhm for regular input 3.3 kOhm for fast input 2.81 kOhm for high speed input |
| Response Time | 35 μs turn-on, I2I5 terminal(s) for fast input 100 μs turn-off, I2I5 terminal(s) for fast input 5 μs turn-on, I0I1 terminal(s) for high speed input 35 μs turn-off, I0I1 terminal(s) for regular input 100 μs turn-off, I6I13 terminal(s) for regular input 10 ms turn-off, I6I13 terminal(s) for relay output 10 ms turn-off, Q0Q11 terminal(s) for relay output 55 μs turn-on, I14I19 terminal(s) for regular input 125 μs turn-off, I14I19 terminal(s) for regular input |

| Configurable Filtening Time | A see for issue |
|---|---|
| Configurable Filtering Time | 0 ms for input 3 ms for input |
| | 12 ms for input |
| Output Voltage Limits | 30 V DC 250 V AC |
| Maximum Current Per Output | 4 A at COM 0 |
| Common | 4 A at COM 1 4 A at COM 2 |
| Electrical Durability | 100000 cycles AC-12, 240 V, 480 VA, resistive 100000 cycles DC-12, 24 V, 48 W, resistive |
| Switching Frequency | 0.1 Hz with maximum load 5 Hz without maximum load |
| Mechanical Durability | 20000000 cycles for relay output |
| Minimum Load | 10 mA at 5 V DC for relay output |
| Memory Capacity | 1024 kB internal flash with 10000 instructions for backup of programs |
| Data Storage Equipment | 32 GB micro SD card (optional) |
| Execution Time For 1 Kinstruction | 0.3 ms for event and periodic task |
| Execution Time Per Instruction | 0.2 μs Boolean |
| Exct Time For Event Task | 60 μs response time |
| Regulation Loop | Adjustable PID regulator up to 14 simultaneous loops |
| Control Signal Type | Quadrature (x1, x2, x4) at 60 kHz for fast input (HSC mode) Pulse/direction at 60 kHz for fast input (HSC mode) Single phase at 60 kHz for fast input (HSC mode) CW/CCW at 60 kHz for fast input (HSC mode) |
| Counting Input Number | 2 fast input (HSC mode) at 60 kHz 32 bits |
| Integrated Connection Type | USB port with mini B USB 2.0 connector Non isolated serial link serial 1 with terminal block connector and RS485 interface Non isolated serial link serial 2 with terminal block connector and RS232/RS485 interface |
| Transmission Rate | 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232 12 Mbit/s for USB |
| Communication Port Protocol | USB port: USB - SoMachine-Network Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network |
| Local Signalling | 1 LED (green) for PWR 1 LED (green) for RUN 1 LED (red) for module error (ERR) 1 LED (green) for SD card access (SD) 1 LED (green) for SL1 1 LED per channel (green) for I/O state |
| Electrical Connection | removable screw terminal blockfor inputs removable screw terminal blockfor outputs removable screw terminal block, 4 terminal(s) for connecting the serial link1 Mini B USB 2.0 connectorfor a programming terminal removable screw terminal block, 3 terminal(s) for connecting the 100-240 V AC power supply |
| Maximum Cable Distance Between Devices | Shielded cable: <10 m for fast input Shielded cable: <10 m for high speed input Unshielded cable: <150 m for output Unshielded cable: <50 m for regular input |
| Insulation | Between input and internal logic at 560 V AC Between fast input and internal logic at 560 V AC Between input groups at 560 V AC Non-insulated between inputs Between output and internal logic at 1780 V AC Between output groups at 1780 V AC Between supply and internal logic at 1780 V AC |
| Sensor Power Supply | 24 V DC |

| Mounting Support | Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 plate or panel with fixing kit conforming to IEC 60715 |
|------------------|---|
| Height | 90 mm |
| Depth | 70 mm |
| Width | 175 mm |
| Net Weight | 0.435 kg |

Environment

| Ip Degree Of Protection | IP20 with protective cover in place |
|--|--|
| Product Certifications | CE |
| Standards | EN/IEC 61010-2-201 |
| | EN/IEC 61131-2 |
| Electromagnetic Compatibility | Electrostatic discharge immunity test - test level: 8 kV (air discharge) conforming to EN/IEC 61000-4-2 |
| | Electrostatic discharge immunity test - test level: 6 kV (contact discharge) conforming to EN/IEC 61000-4-2 |
| | Susceptibility to electromagnetic fields - test level: 10 V/m (80 MHz3 GHz) conforming to EN/IEC 61000-4-3 |
| | Conducted emission - test level: 79 dBµV/m QP/66 dBµV/m AV (power lines (AC)) conforming to EN/IEC 55011 |
| | Conducted emission - test level: 73 dBµV/m QP/60 dBµV/m AV (power lines (AC)) conforming to EN/IEC 55011 |
| | Radiated emission - test level: 40 dBµV/m QP class A (10 m) conforming to EN/IEC 55011 |
| | Radiated emission - test level: 47 dBµV/m QP class A (10 m) conforming to EN/IEC 55011 |
| | Magnetic field at power frequency - test level: 30 A/m (I/O) conforming to EN/IEC 61000-4-8 |
| | Electrical fast transient/burst immunity test - test level: 2 kV (power lines) conforming to EN/IEC 61000-4-4 |
| | Electrical fast transient/burst immunity test - test level: 2 kV (relay output) conforming to EN/IEC 61000-4-4 |
| | Electrical fast transient/burst immunity test - test level: 1 kV (I/O) conforming to EN/ IEC 61000-4-4 |
| | Electrical fast transient/burst immunity test - test level: 1 kV (serial link) conforming to EN/IEC 61000-4-4 |
| | 1.2/50 μs shock waves immunity test - test level: 1 kV (power lines (DC)) conforming to EN/IEC 61000-4-5 |
| | 1.2/50 μs shock waves immunity test - test level: 2 kV (power lines (AC)) conforming to EN/IEC 61000-4-5 |
| | 1.2/50 μs shock waves immunity test - test level: 2 kV (relay output) conforming to EN/IEC 61000-4-5 |
| | 1.2/50 μs shock waves immunity test - test level: 1 kV (I/O) conforming to EN/IEC 61000-4-5 |
| | $1.2/50\ \mu s$ shock waves immunity test - test level: 1 kV (shielded cable) conforming to EN/IEC 61000-4-5 |
| | 1.2/50 μs shock waves immunity test - test level: 0.5 kV class A (power lines (DC)) conforming to EN/IEC 61000-4-5 |
| | 1.2/50 μs shock waves immunity test - test level: 1 kV class A (power lines (AC)) conforming to EN/IEC 61000-4-5 |
| | 1.2/50 μs shock waves immunity test - test level: 1 kV (relay output) conforming to EN/IEC 61000-4-5 |
| | Conducted RF disturbances - test level: 10 V (0.1580 MHz) conforming to EN/IEC 61000-4-6 |
| Shock Resistance | 15 gn for 11 ms |
| | 30 gn for 6 ms |
| Immunity To Microbreaks | 10 ms |
| Vibration Resistance | 3.5 mm at 5…8.4 Hz on symmetrical rail 1 gn at 8.4…150 Hz on symmetrical rail |
| | 3.5 mm at 58.4 Hz on panel mounting |
| | 3 gn at 8.4150 Hz on panel mounting |
| Relative Humidity | 1095 %, without condensation (in operation) |
| - , | 1095 %, without condensation (in storage) |
| Ambient Air Temperature For Operation | 055 °C (horizontal installation) |

Life Is On Scheider

| Ambient Air Temperature For Storage | -2570 °C |
|--|----------|
| Pollution Degree | <= 2 |
| Operating Altitude | 02000 m |
| Storage Altitude | 03000 m |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 9.312 cm |
| Package 1 Width | 13.703 cm |
| Package 1 Length | 18.69 cm |
| Package 1 Weight | 640.0 g |
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 12 |
| Package 2 Height | 30.0 cm |
| Package 2 Width | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 8.036 kg |
| Unit Type Of Package 3 | P12 |
| Number Of Units In Package 3 | 288 |
| Package 3 Height | 95.0 cm |
| Package 3 Width | 80.0 cm |
| Package 3 Length | 120.0 cm |
| Package 3 Weight | 132.0 kg |

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |

Product datasheet

Dimensions Drawings

Dimensions Drawings

Dimensions

