Product datasheet





module XPSVN - zero speed detection - 24 V DC for motor power supply <= 60 Hz

XPSVNE1142P

Discontinued on: 16 Jan 2024

① Discontinued

Main

Range Of Product	Preventa Safety automation
Product Or Component Type	Preventa safety module
Safety Module Name	XPSVNE
Safety Module Application	For zero speed detection
Function Of Module	Monitoring 3-phase motor with star-delta starting Monitoring 3-phase motor with variable number of poles and star-delta starting Monitoring 3-phase motor + variable speed drive Monitoring 3-phase motor Monitoring XPS AK Monitoring star-delta motor starter and guard switch type XCS E Monitoring dc motor
Safety Level	Can reach PL d/category 3 conforming to EN/ISO 13849-1 Can reach SILCL 2 conforming to EN/IEC 62061
Safety Reliability Data	MTTFd = 124.1 years conforming to EN/ISO 13849-1 DC > 99 % conforming to EN/ISO 13849-1 PFHd = 9.26E-9 1/h conforming to EN/IEC 62061
Product Certifications	CSA UL TÜV
[Us] Rated Supply Voltage	24 V DC - 1510 %
Output Type	Relay, 1 NO + 1 NC circuit(s), volt-free
Number Of Additional Circuits	2 solid state outputs

Complementary

Product Destination	For motor power supply <= 60 Hz	
Maximum Power Consumption In W	3.5 W	
Input Voltage	500 Vrms	
Input Detection Threshold	0.010.1 V	
Breaking Capacity	180 VA holding AC-15 C300 relay output 1800 VA inrush AC-15 C300 relay output	
Breaking Capacity	1.2 A at 24 V (DC-13) time constant: 50 ms for NC relay output circuit1.5 A at 24 V (DC-13) time constant: 50 ms for NO relay output circuit10 mA at 48 V for solid state output circuit20 mA at 24 V for solid state output circuit	
Ith] Conventional Free Air 2.5 A for relay output Thermal Current		
Associated Fuse Rating	4 A gG for relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200	
Standards	EN/IEC 60947-5-1 EN/IEC 60204-1	

Minimum Output Current	10 mA for relay output	
Minimum Output Voltage	17 V for relay output	
[Ui] Rated Insulation Voltage	300 V (pollution degree 2) conforming to IEC 60947-5-1 300 V (pollution degree 2) conforming to DIN VDE 0110 parts 1 and 2	
[Uimp] Rated Impulse Withstand Voltage	4 kV overvoltage category III conforming to IEC 60947-5-1 4 kV overvoltage category III conforming to DIN VDE 0110 parts 1 and 2	
Local Signalling	4 LEDs	
Connections - Terminals	Captive screw clamp terminals, removable terminal block flexible cable: 0.21.5 mm² without cable end, 2 wires	
	Captive screw clamp terminals, removable terminal block flexible cable: 0.22.5 mm	
	without cable end, 1 wire Captive screw clamp terminals, removable terminal block flexible cable: 0.251 mm ²	
	with cable end, without bezel, 2 wires	
	Captive screw clamp terminals, removable terminal block flexible cable: 0.252.5 mm² with cable end, with bezel, 1 wire	
	Captive screw clamp terminals, removable terminal block flexible cable: 0.252.5	
	mm² with cable end, without bezel, 1 wire Captive screw clamp terminals, removable terminal block flexible cable: 0.51.5 mm²	
	with cable end, with double bezel, 2 wires	
	Captive screw clamp terminals, removable terminal block solid cable: 0.21 mm² without cable end, 2 wires	
	Captive screw clamp terminals, removable terminal block solid cable: 0.22.5 mm ² without cable end, 1 wire	
Mounting Support	35 mm symmetrical DIN rail	
Depth	114 mm	
Height	99 mm	
Width	45 mm	

Environment

Ip Degree Of Protection	IP20 (terminals) conforming to EN/IEC 60529 IP40 (enclosure) conforming to EN/IEC 60529
Ambient Air Temperature For Operation	-1055 °C
Ambient Air Temperature For	-2585 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	12.5 cm
Package 1 Length	6.5 cm
Package 1 Weight	286.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	12
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	192

Package 3 Height	75 cm	
Package 3 Width	40 cm	
Package 3 Length	80 cm	
Package 3 Weight	72 ka	

Contractual warranty

Warranty 18 months

Sustainability Green Premium*

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
②	Rohs Exemption Information	Yes
	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	