



# Controller M200 16I/O transistor Source

TM200C16T

## Main

| Range Of Product            | Easy Modicon M200   |
|-----------------------------|---|
| Product Or Component Type   | Logic controller  |
| [Us] Rated Supply Voltage   | 24 V DC   |
| Discrete I/O Number         | 16  |
| Discrete Input Number       | I8: 1 regular input<br>I2I5: 4 fast input<br>I0, I1, I6, I7: 4 high speed input |
| Discrete Output Number      | Q2Q6: 5 transistor output<br>Q0Q1: 2 fast output (PLS/PWM/PTO mode)             |
| Discrete Input Voltage      | 24 V  |
| Discrete Input Voltage Type | DC  |
| Discrete Input Current      | 7 mA for input  |
| Discrete Input Logic        | Sink or source (positive/negative) type 1 conforming to IEC 61131-2             |
| Discrete Output Voltage     | 24 V DC   |
| Discrete Output Current     | 0.5 A   |
| Discrete Output Type        | Transistor  |
| Discrete Output Logic       | Positive logic (source)   |
| Power Consumption In W      | 15.5 W at 24 V DC (with max I/O)  |

## Complementary

| Maximum Number Of I/O<br>Expansion Module | 4 with 135 discrete output(s) for transistor output 4 with 64 discrete output(s) for relay output |
|---|---|
| Supply Voltage Limits                     | 20.428.8 V  |
| Inrush Current                            | 35 A  |
| Voltage State 1 Guaranteed                | >= 15 V for input   |
| Voltage State 0 Guaranteed                | <= 5 V for input  |
| Input Impedance                           | 3.3 kOhm for discrete input   |
| Response Time                             | 1 ms turn-on, Q0Q6 terminal(s) for output   |
|   | 1 ms turn-off, Q0Q7 terminal(s) for output  |
|   | 5 μs turn-off, I0, I1, I6, I7 terminal(s) for high speed input                                    |
|   | 5 μs turn-on, I0, I1, I6, I7 terminal(s) for high speed input                                     |
|   | 100 μs turn-off, I2I5 terminal(s) for fast input  |
|   | 35 μs turn-on, I2I5 terminal(s) for fast input  |
|   | 100 μs turn-off, l8 terminal(s) for regular input   |
|   | 35 μs turn-on, l8 terminal(s) for regular input   |
| Configurable Filtering Time               | 0 ms for input  |
|   | 3 ms for input  |
|   | 12 ms for input   |

| Maximum Current Per Output Common         | 3.5 A at COM 0  |
|---|---|
| Output Frequency                          | 100 kHz for fast output (PWM/PLS mode) at Q0Q1  |
| Maximum Leakage Current                   | 0.1 mA for transistor output  |
| Maximum Voltage Drop                      | <1 V  |
| Maximum Tungsten Load                     | <12 W for output and fast output  |
| Protection Type                           | Overload and short-circuit protection at 2 A  |
| Reset Time                                | 1 s automatic reset   |
| Memory Capacity                           | 512 byte internal flash for backup of programs  |
| Data Storage Equipment                    | 32 GB micro SD card (optional)  |
| Battery Type                              | BR2032 Li-CFx (Lithium-Carbon Monofluoride), battery life: 5 year(s)  |
| Backup Time                               | 3 years at 25 °C (by interruption of power supply)  |
| Execution Time For 1 Kinstruction         | 0.3 ms for event and periodic task  |
| Execution Time Per Instruction            | 0.2 μs Boolean  |
| Exct Time For Event Task                  | 60 μs response time   |
| Clock Drift                               | <= 90 s/month at 25 °C  |
| Regulation Loop                           | Adjustable PID regulator up to 14 simultaneous loops  |
| Positioning Functions                     | PWM/PLS 2 channel(s) at 100 kHz   |
| Control Signal Type                       | Quadrature (x1, x2, x4) at 100 kHz for fast input (HSC mode) Pulse/direction at 100 kHz for fast input (HSC mode) Single phase at 100 kHz for fast input (HSC mode) CW/CCW at 100 kHz for fast input (HSC mode)   |
| Counting Input Number                     | 4 fast input (HSC mode) at 100 kHz 32 bits  |
| Integrated Connection Type                | USB port with mini B USB 2.0 connector  Non isolated serial link serial 1 with terminal block connector and RS485 interface  Non isolated serial link serial 2 with terminal block connector and RS232/RS485 interface  Isolated serial link serial 2 with terminal block connector and RS485 interface   |
| Transmission Rate                         | 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232 12 Mbit/s for USB  |
| Communication Port Protocol               | USB port: USB - SoMachine-Network Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network  |
| Local Signalling                          | 1 LED (green) for PWR 1 LED (green) for RUN 1 LED (red) for module error (ERR) 1 LED (green) for SD card access (SD) 1 LED (red) for BAT 1 LED (green) for SL1 1 LED per channel (green) for I/O state  |
| Electrical Connection                     | Mini B USB 2.0 connectorfor a programming terminal removable screw terminal blockfor inputs removable screw terminal blockfor outputs removable screw terminal block, 3 terminal(s) for connecting the 24 V DC power supply removable screw terminal block, 4 terminal(s) for connecting the serial link1 |
| Maximum Cable Distance<br>Between Devices | Unshielded cable: <50 m for input Shielded cable: <10 m for fast input Shielded cable: <10 m for high speed input Unshielded cable: <150 m for output   |

| Insulation       | Non-insulated between inputs  Between input and internal logic at 500 V AC  Between fast input and internal logic at 500 V AC  Between input groups at 500 V AC  Between output and internal logic at 500 V AC  Between output groups at 500 V AC  Between supply and internal logic at 500 V DC |
|------------------|--|
| Marking          | CE   |
| Mounting Support | Top hat type TH35-15 rail conforming to IEC 60715  Top hat type TH35-7.5 plate or panel with fixing kit conforming to IEC 60715  |
| Height           | 90 mm  |
| Depth            | 70 mm  |
| Width            | 110 mm   |
| Net Weight       | 0.365 kg   |

## **Environment**

| Ip Degree Of Protection       | IP20 with protective cover in place   |
|-------------------------------|---|
| <br>Standards                 | IEC 61131-2   |
|                               | IEC 61010-2-201   |
| Electromagnetic Compatibility | Electrostatic discharge immunity test - test level: 8 kV (air discharge) conforming to                      |
|                               | IEC 61000-4-2   |
|                               | Electrostatic discharge immunity test - test level: 6 kV (contact discharge) conforming to IEC 61000-4-2    |
|                               | Susceptibility to electromagnetic fields - test level: 10 V/m (80 MHz3 GHz) conforming to IEC 61000-4-3     |
|                               | Magnetic field at power frequency - test level: 30 A/m conforming to IEC 61000-4-8                          |
|                               | Electrical fast transient/burst immunity test - test level: 2 kV (power lines) conforming                   |
|                               | to IEC 61000-4-4  |
|                               | Electrical fast transient/burst immunity test - test level: 2 kV (relay output) conforming to IEC 61000-4-4 |
|                               | Electrical fast transient/burst immunity test - test level: 1 kV (I/O) conforming to IEC 61000-4-4          |
|                               | Electrical fast transient/burst immunity test - test level: 1 kV (serial link) conforming to IEC 61000-4-4  |
|                               | $1.2/50~\mu s$ shock waves immunity test - test level: 1 kV (power lines (DC)) conforming to IEC 61000-4-5  |
|                               | 1.2/50 µs shock waves immunity test - test level: 2 kV (power lines (AC)) conforming to IEC 61000-4-5       |
|                               | 1.2/50 µs shock waves immunity test - test level: 2 kV (relay output) conforming to IEC 61000-4-5           |
|                               | 1.2/50 µs shock waves immunity test - test level: 1 kV (I/O) conforming to IEC 61000-4-5                    |
|                               | 1.2/50 µs shock waves immunity test - test level: 1 kV (shielded cable) conforming to IEC 61000-4-5         |
|                               | 1.2/50 μs shock waves immunity test - test level: 0.5 kV (power lines (DC)) conforming to IEC 61000-4-5     |
|                               | 1.2/50 µs shock waves immunity test - test level: 1 kV (power lines (AC)) conforming to IEC 61000-4-5       |
|                               | Conducted RF disturbances - test level: 10 V (0.1580 MHz) conforming to IEC 61000-4-6                       |
|                               | Conducted emission - test level: 79 dBµV/m QP/66 dBµV/m AV (power lines (AC)) conforming to IEC 55011       |
|                               | Conducted emission - test level: 73 dBµV/m QP/60 dBµV/m AV (power lines (AC)) conforming to IEC 55011       |
|                               | Radiated emission - test level: 40 dBµV/m QP class A (10 m) conforming to IEC 55011                         |
|                               | Radiated emission - test level: 47 dBµV/m QP class A (10 m) conforming to IEC                               |
|                               | 55011   |
| Shock Resistance              | 15 gn for 11 ms   |
|                               | 30 gn for 6 ms  |
| Immunity To Microbreaks       | 2 ms  |
| Vibration Resistance          | 3.5 mm at 58.4 Hz on symmetrical rail   |
|                               | 1 gn at 8.4150 Hz on symmetrical rail   |
|                               | 3.5 mm at 58.7 Hz on panel mounting   |
|                               | 2 gn at 8.7150 Hz on panel mounting   |
|                               |   |

| Relative Humidity                     | 1095 %, without condensation (in operation) 1095 %, without condensation (in storage) |
|---------------------------------------|---|
| Ambient Air Temperature For Operation | 055 °C (horizontal installation)  |
| Ambient Air Temperature For Storage   | -2570 °C  |
| Pollution Degree                      | <= 2  |
| Operating Altitude                    | 02000 m   |
| Storage Altitude                      | 03000 m   |

# **Packing Units**

| Unit Type Of Package 1       | PCE      |
|------------------------------|----------|
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 13.6 cm  |
| Package 1 Width              | 9 cm     |
| Package 1 Length             | 11.8 cm  |
| Package 1 Weight             | 517 g    |
| Unit Type Of Package 2       | S03      |
| Number Of Units In Package 2 | 18       |
| Package 2 Height             | 30 cm    |
| Package 2 Width              | 30 cm    |
| Package 2 Length             | 40 cm    |
| Package 2 Weight             | 9906 g   |
| Unit Type Of Package 3       | P12      |
| Number Of Units In Package 3 | 432      |
| Package 3 Height             | 80 cm    |
| Package 3 Width              | 120 cm   |
| Package 3 Length             | 105 cm   |
| Package 3 Weight             | 246744 g |



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

## **Certifications & Standards**


| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation    | China RoHS declaration  |
| Environmental Disclosure | Product Environmental Profile   |
| Weee                     | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile      | End of Life Information   |


## TM200C16T

**Dimensions Drawings** 

# Dimensions Drawings

#### **Dimensions**







Mounting and Clearance

## Mounting and Clearance

### Mounting on a Rail




### **Direct Mounting on a Panel Surface**



## **Mounting Position**

# **Product datasheet**

## TM200C16T













Clearance





TMCR2•••Installation




## **Product datasheet**

## TM200C16T










TMCR2 ••• De-Installation

17 May 2024








# **Product datasheet**


## TM200C16T




#### Connections and Schema

## Wiring Diagram / Connections Schema


### **DC Power Supply**



#### Digital Inputs (Sink or Source)




\*\* 10...18



- (\*) Type T fuse
- (\*\*) Fast inputs
  A Sink wiring (positive logic)
- B Source wiring (negative logic)

#### Regular and Fast Transistor Output




\*\* Q0...Q6



- (\*) Type T fuse
- (\*\*) Fast outputs

#### **USB Mini-B Connection**

### TM200C16T



#### **SL1 Connection**

