



# controller M200 40 IO transistor Source

TM200C40T

### Main

Range Of Product	Easy Modicon M200
Product Or Component Type	Logic controller
[Us] Rated Supply Voltage	24 V DC
Discrete I/O Number	40
Discrete Input Number	I2I5: 4 fast input I0, I1, I6, I7: 4 high speed input I8I23: 16 regular input
Discrete Output Number	Q0Q1: 2 fast output (PLS/PWM/PTO mode) Q2Q15: 14 transistor output
Discrete Input Voltage	24 V
Discrete Input Voltage Type	DC
Discrete Input Current	7 mA for input
Discrete Input Logic	Sink or source (positive/negative) type 1 conforming to IEC 61131-2
Discrete Output Voltage	24 V DC
Discrete Output Current	0.5 A
Discrete Output Type	Transistor
Discrete Output Logic	Positive logic (source)
Power Consumption In W	18 W at 24 V DC (with max I/O)

## Complementary

Maximum Number Of I/O Expansion Module	4 with 64 discrete output(s) for relay output 4 with 144 discrete output(s) for transistor output	
Supply Voltage Limits	20.428.8 V	
Inrush Current	35 A	
Voltage State 1 Guaranteed	>= 15 V for input	
Voltage State 0 Guaranteed	<= 5 V for input	
Input Impedance	3.3 kOhm for discrete input	
Response Time	35 μs turn-on, I2I5 terminal(s) for input 100 μs turn-off, I2I5 terminal(s) for input	

5 μs turn-on, 10, 11, 16, 17 terminal(s) for fast input 5 μs turn-off, 10, 11, 16, 17 terminal(s) for fast input 35 μs turn-off, 18...113 terminal(s) for input 100 μs turn-off, 18...113 terminal(s) for input 55 μs turn-on, 114...123 terminal(s) for input 125 μs turn-off, 114...123 terminal(s) for input 1 ms turn-off, Q0...Q15 terminal(s) for output 1 ms turn-off, Q0...Q15 terminal(s) for output

O	
Configurable Filtering Time	0 ms for input 3 ms for input
	12 ms for input
Maximum Current Per Output Common	2 A at COM 0
Common	2 A at COM 1 4 A at COM 2
Output Frequency	100 kHz for fast output (PWM/PLS mode) at Q0Q1
Maximum Leakage Current	0.1 mA for transistor output
Maximum Voltage Drop	<1 V
Maximum Tungsten Load	<12 W for output and fast output
Protection Type	Overload and short-circuit protection at 2 A
Reset Time	1 s automatic reset
Memory Capacity	512 byte internal flash for backup of programs
Data Storage Equipment	32 GB micro SD card (optional)
Battery Type	BR2032 Li-CFx (Lithium-Carbon Monofluoride), battery life: 5 year(s)
Backup Time	3 years at 25 °C (by interruption of power supply)
Execution Time For 1 Kinstruction	0.3 ms for event and periodic task
Execution Time Per Instruction	0.2 μs Boolean
Exct Time For Event Task	60 μs response time
Clock Drift	<= 90 s/month at 25 °C
Regulation Loop	Adjustable PID regulator up to 14 simultaneous loops
Positioning Functions	PWM/PLS 2 channel(s) at 100 kHz
Control Signal Type	Quadrature (x1, x2, x4) at 100 kHz for fast input (HSC mode)
	Pulse/direction at 100 kHz for fast input (HSC mode) Single phase at 100 kHz for fast input (HSC mode)
	CW/CCW at 100 kHz for fast input (HSC mode)
Counting Input Number	4 fast input (HSC mode) at 100 kHz 32 bits
Integrated Connection Type	USB port with mini B USB 2.0 connector
	Non isolated serial link serial 1 with terminal block connector and RS485 interface  Non isolated serial link serial 2 with terminal block connector and RS232/RS485
	interface
	Isolated serial link serial 2 with terminal block connector and RS485 interface
Transmission Rate	1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232
	12 Mbit/s for USB
Communication Port Protocol	USB port: USB - SoMachine-Network Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network
Local Signalling	1 LED (green) for PWR
	1 LED (green) for RUN 1 LED (rod) for modula error (EDD)
	1 LED (red) for module error (ERR) 1 LED (green) for SD card access (SD)
	1 LED (red) for BAT
	1 LED (green) for SL1 1 LED per channel (green) for I/O state
Electrical Connection	Mini B USB 2.0 connectorfor a programming terminal
	removable screw terminal blockfor inputs removable screw terminal blockfor outputs
	removable screw terminal block, 3 terminal(s) for connecting the 24 V DC power
	supply removable screw terminal block, 4 terminal(s) for connecting the serial link1
Maximum Cable Distance	Unshielded cable: <50 m for input
Between Devices	Shielded cable: <10 m for fast input
	Shielded cable: <10 m for high speed input Unshielded cable: <150 m for output

Insulation	Non-insulated between inputs Between input and internal logic at 500 V AC Between fast input and internal logic at 500 V AC Between input groups at 500 V AC Between output and internal logic at 500 V AC Between output groups at 500 V AC Between output groups at 500 V AC Between supply and internal logic at 500 V DC
Marking	CE
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715  Top hat type TH35-7.5 plate or panel with fixing kit conforming to IEC 60715
Height	90 mm
Depth	70 mm
Width	175 mm
Net Weight	0.522 kg

## **Environment**

Ip Degree Of Protection	IP20 with protective cover in place
Standards	IEC 61131-2 IEC 61010-2-201
Electromagnetic Compatibility	Electrostatic discharge immunity test - test level: 8 kV (air discharge) conforming to IEC 61000-4-2
	Electrostatic discharge immunity test - test level: 6 kV (contact discharge) conforming to IEC 61000-4-2
	Susceptibility to electromagnetic fields - test level: 10 V/m (80 MHz3 GHz) conforming to IEC 61000-4-3
	Magnetic field at power frequency - test level: 30 A/m conforming to IEC 61000-4-8 Electrical fast transient/burst immunity test - test level: 2 kV (power lines) conforming to IEC 61000-4-4
	Electrical fast transient/burst immunity test - test level: 2 kV (relay output) conforming to IEC 61000-4-4
	Electrical fast transient/burst immunity test - test level: 1 kV (I/O) conforming to IEC 61000-4-4
	Electrical fast transient/burst immunity test - test level: 1 kV (serial link) conforming to IEC 61000-4-4
	$1.2/50~\mu s$ shock waves immunity test - test level: 1 kV (power lines (DC)) conforming to IEC 61000-4-5
	$1.2/50~\mu s$ shock waves immunity test - test level: 2 kV (power lines (AC)) conforming to IEC 61000-4-5
	1.2/50 µs shock waves immunity test - test level: 2 kV (relay output) conforming to IEC 61000-4-5
	1.2/50 µs shock waves immunity test - test level: 1 kV (I/O) conforming to IEC 61000-4-5
	1.2/50 µs shock waves immunity test - test level: 1 kV (shielded cable) conforming to IEC 61000-4-5
	1.2/50 µs shock waves immunity test - test level: 0.5 kV (power lines (DC)) conforming to IEC 61000-4-5
	1.2/50 µs shock waves immunity test - test level: 1 kV (power lines (AC)) conforming to IEC 61000-4-5
	Conducted RF disturbances - test level: 10 V (0.1580 MHz) conforming to IEC 61000-4-6
	Conducted emission - test level: 79 dBμV/m QP/66 dBμV/m AV (power lines (AC)) conforming to IEC 55011
	Conducted emission - test level: 73 dBμV/m QP/60 dBμV/m AV (power lines (AC)) conforming to IEC 55011
	Radiated emission - test level: 40 dBμV/m QP class A (10 m) conforming to IEC 55011
	Radiated emission - test level: 47 dB $\mu$ V/m QP class A (10 m) conforming to IEC 55011
Shock Resistance	15 gn for 11 ms 30 gn for 6 ms
Immunity To Microbreaks	2 ms
Vibration Resistance	3.5 mm at 58.4 Hz on symmetrical rail 1 gn at 8.4150 Hz on symmetrical rail
	3.5 mm at 58.7 Hz on panel mounting
	2 gn at 8.7150 Hz on panel mounting

Relative Humidity	1095 %, without condensation (in operation) 1095 %, without condensation (in storage)
Ambient Air Temperature For Operation	055 °C (horizontal installation)
Ambient Air Temperature For Storage	-2570 °C
Pollution Degree	<= 2
Operating Altitude	02000 m
Storage Altitude	03000 m

# **Packing Units**

PCE
1
9 cm
18.3 cm
13.6 cm
765.5 g
\$03
12
30 cm
30 cm
40 cm
9686 g
P12
288
95 cm
80 cm
120 cm
241464 g



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

## **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information


## TM200C40T

## **Dimensions Drawings**

## **Dimensions Drawings**

#### **Dimensions**







Mounting and Clearance

## Mounting and Clearance

### Mounting on a Rail




## **Direct Mounting on a Panel Surface**




### **Mounting Position**

## TM200C40T




## TM200C40T












Clearance





#### TMCR2•••Installation




## TM200C40T










TMCR2 ••• De-Installation








## TM200C40T




#### Connections and Schema

#### Wiring Diagram / Connections Schema


#### **DC Power Supply**



#### Digital Inputs (Sink or Source)




\*\* 10...17



- (\*) Type T fuse
- (\*\*) Fast inputs
- A Sink wiring (positive logic)
- B Source wiring (negative logic)
- (1) The COM0 and COM1 terminals are **not** connected internally.

#### **Regular and Fast Transistor Output**



\*\* Q0...Q3




- (\*) Type T fuse
- (\*\*) Fast outputs
- (1) The V0+, V1+ and V2+ terminals are not connected internally.

### TM200C40T

(2) The V0-, V1- and V2- terminals are not connected internally.

### **USB Mini-B Connection**



#### **SL1 Connection**

