



controller, Modicon Easy M200, 40 IO, transistor source, Ethernet

TM200CE40T

Main

| Range Of Product | Easy Modicon M200 |
|-----------------------------|---|
| Product Or Component Type | Logic controller |
| [Us] Rated Supply Voltage | 24 V DC |
| Discrete I/O Number | 40 |
| Discrete Input Number | I2I5: 4 fast input I0, I1, I6, I7: 4 high speed input I8I23: 16 regular input |
| Discrete Output Number | Q0Q1: 2 fast output (PLS/PWM/PTO mode) Q2Q15: 14 transistor output |
| Discrete Input Voltage | 24 V |
| Discrete Input Voltage Type | DC |
| Discrete Input Current | 7 mA for input |
| Discrete Input Logic | Sink or source (positive/negative) type 1 conforming to IEC 61131-2 |
| Discrete Output Voltage | 24 V DC |
| Discrete Output Current | 0.5 A |
| Discrete Output Type | Transistor |
| Discrete Output Logic | Positive logic (source) |
| Power Consumption In W | 18 W at 24 V DC (with max I/O) |

Complementary

| Maximum Number Of I/O Expansion Module | 4 with 64 discrete output(s) for relay output 4 with 144 discrete output(s) for transistor output |
|--|---|
| Supply Voltage Limits | 20.428.8 V |
| Inrush Current | 35 A |
| Voltage State 1 Guaranteed | >= 15 V for input |
| Voltage State 0 Guaranteed | <= 5 V for input |
| Input Impedance | 3.3 kOhm for discrete input |
| Response Time | 1 ms turn-on, Q0Q15 terminal(s) for output 1 ms turn-off, Q0Q15 terminal(s) for output 5 µs turn-off, I0, I1, I6, I7 terminal(s) for high speed input 5 µs turn-on, I0, I1, I6, I7 terminal(s) for high speed input 100 µs turn-off, I2I5 terminal(s) for fast input 35 µs turn-on, I2I5 terminal(s) for fast input 100 µs turn-off, I8I13 terminal(s) for regular input 35 µs turn-on, I8I13 terminal(s) for regular input |

125 µs turn-off, I14...I23 terminal(s) for regular input 55 μs turn-on, I14...I23 terminal(s) for regular input

Life Is On Schneider 15 May 2024

| Configurable Filtering Time | 0 ms for input 3 ms for input 12 ms for input |
|--------------------------------------|---|
| Maximum Current Per Output Common | 2 A 4 A |
| Output Frequency | 100 kHz for fast output (PWM/PLS mode) at Q0Q1 |
| Maximum Leakage Current | 0.1 mA for transistor output |
| Maximum Voltage Drop | <1 V |
| Maximum Tungsten Load | <12 W for output and fast output |
| Protection Type | Overload and short-circuit protection at 2 A |
| Reset Time | 1 s automatic reset |
| Memory Capacity | 512 byte internal flash for backup of programs |
| Data Storage Equipment | 32 GB micro SD card (optional) |
| Battery Type | BR2032 Li-CFx (Lithium-Carbon Monofluoride), battery life: 5 year(s) |
| Backup Time | 3 years at 25 °C (by interruption of power supply) |
| Execution Time For 1 Kinstruction | 0.3 ms for event and periodic task |
| Execution Time Per Instruction | 0.2 μs Boolean |
| Exct Time For Event Task | 60 μs response time |
| Clock Drift | <= 90 s/month at 25 °C |
| Regulation Loop | Adjustable PID regulator up to 14 simultaneous loops |
| Positioning Functions | PWM/PLS 2 channel(s) at 100 kHz |
| Control Signal Type | Quadrature (x1, x2, x4) at 100 kHz for fast input (HSC mode) Pulse/direction at 100 kHz for fast input (HSC mode) Single phase at 100 kHz for fast input (HSC mode) CW/CCW at 100 kHz for fast input (HSC mode) |
| Counting Input Number | 4 fast input (HSC mode) at 100 kHz 32 bits |
| Integrated Connection Type | USB port with mini B USB 2.0 connector Non isolated serial link serial 1 with terminal block connector and RS485 interface Non isolated serial link serial 2 with terminal block connector and RS232/RS485 interface Ethernet Modbus TCP/IP Ethernet with RJ45 connector and 1 Ethernet port 10/100BASE-T interface Isolated serial link serial 2 with terminal block connector and RS485 interface |
| Transmission Rate | 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232 12 Mbit/s for USB 10/100 Mbit/s for bus length of 100 m for Ethernet Modbus TCP/IP |
| Communication Port Protocol | USB port: USB - SoMachine-Network Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network Ethernet Modbus TCP/IP: Modbus TCP/IP client/server |
| Local Signalling | 1 LED (green) for PWR 1 LED (green) for RUN 1 LED (red) for module error (ERR) 1 LED (green) for SD card access (SD) 1 LED (red) for BAT 1 LED (green) for SL1 1 LED per channel (green) for I/O state 2 LEDs (green) for communication (LK/ACT 10/100) |
| Electrical Connection | Mini B USB 2.0 connectorfor a programming terminal RJ45 connectorfor connecting Ethernet network removable screw terminal blockfor inputs removable screw terminal blockfor outputs removable screw terminal block, 3 terminal(s) for connecting the 24 V DC power supply removable screw terminal block, 4 terminal(s) for connecting the serial link1 |

| Maximum Cable Distance Between Devices | Unshielded cable: <50 m for input Shielded cable: <10 m for fast input Shielded cable: <10 m for high speed input Unshielded cable: <150 m for output |
|---|--|
| Insulation | Non-insulated between inputs Between input and internal logic at 500 V AC Between fast input and internal logic at 500 V AC Between input groups at 500 V AC Between output and internal logic at 500 V AC Between output groups at 500 V AC Between supply and internal logic at 500 V DC |
| Marking | CE |
| Mounting Support | Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 plate or panel with fixing kit conforming to IEC 60715 |
| Height | 90 mm |
| Depth | 70 mm |
| Width | 175 mm |
| Net Weight | 0.523 kg |

Environment

| Ip Degree Of Protection | IP20 with protective cover in place |
|-------------------------------|---|
| Standards | IEC 61131-2 IEC 61010-2-201 |
| Electromagnetic Compatibility | Electrostatic discharge immunity test - test level: 8 kV (air discharge) conforming to IEC 61000-4-2 |
| | Electrostatic discharge immunity test - test level: 6 kV (contact discharge) conforming to IEC 61000-4-2 |
| | Susceptibility to electromagnetic fields - test level: 10 V/m (80 MHz3 GHz) conforming to IEC 61000-4-3 |
| | Magnetic field at power frequency - test level: 30 A/m conforming to IEC 61000-4-8 Electrical fast transient/burst immunity test - test level: 2 kV (power lines) conforming to IEC 61000-4-4 |
| | Electrical fast transient/burst immunity test - test level: 2 kV (relay output) conforming to IEC 61000-4-4 |
| | Electrical fast transient/burst immunity test - test level: 1 kV (I/O) conforming to IEC 61000-4-4 |
| | Electrical fast transient/burst immunity test - test level: 1 kV (serial link) conforming to IEC 61000-4-4 |
| | 1.2/50 µs shock waves immunity test - test level: 1 kV (power lines (DC)) conforming to IEC 61000-4-5 |
| | 1.2/50 µs shock waves immunity test - test level: 2 kV (power lines (AC)) conforming to IEC 61000-4-5 |
| | 1.2/50 µs shock waves immunity test - test level: 2 kV (relay output) conforming to IEC 61000-4-5 |
| | 1.2/50 µs shock waves immunity test - test level: 1 kV (I/O) conforming to IEC 61000-4-5 |
| | 1.2/50 µs shock waves immunity test - test level: 1 kV (shielded cable) conforming to IEC 61000-4-5 |
| | 1.2/50 µs shock waves immunity test - test level: 0.5 kV (power lines (DC)) conforming to IEC 61000-4-5 |
| | 1.2/50 µs shock waves immunity test - test level: 1 kV (power lines (AC)) conforming to IEC 61000-4-5 |
| | Conducted RF disturbances - test level: 10 V (0.1580 MHz) conforming to IEC 61000-4-6 |
| | Conducted emission - test level: 79 dBµV/m QP/66 dBµV/m AV (power lines (AC)) conforming to IEC 55011 |
| | Conducted emission - test level: 73 dBµV/m QP/60 dBµV/m AV (power lines (AC)) conforming to IEC 55011 |
| | Radiated emission - test level: 40 dBµV/m QP class A (10 m) conforming to IEC 55011 |
| | Radiated emission - test level: 47 dBμV/m QP class A (10 m) conforming to IEC |
| | 55011 Electrical fast transient/burst immunity test - test level: 1 kV (Ethernet line) conforming to IEC 61000-4-4 |
| Shock Resistance | 15 gn for 11 ms |

Shock Resistance

15 gn for 11 ms 30 gn for 6 ms

| Immunity To Microbreaks | 2 ms |
|---------------------------------------|---|
| Vibration Resistance | 3.5 mm at 58.4 Hz on symmetrical rail 1 gn at 8.4150 Hz on symmetrical rail 3.5 mm at 58.7 Hz on panel mounting 2 gn at 8.7150 Hz on panel mounting |
| Relative Humidity | 1095 %, without condensation (in operation) 1095 %, without condensation (in storage) |
| Ambient Air Temperature For Operation | 055 °C (horizontal installation) |
| Ambient Air Temperature For Storage | -2570 °C |
| Pollution Degree | <= 2 |
| Operating Altitude | 02000 m |
| Storage Altitude | 03000 m |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 9.63 cm |
| Package 1 Width | 13.735 cm |
| Package 1 Length | 18.785 cm |
| Package 1 Weight | 766 g |
| Unit Type Of Package 2 | S03 |
| Number Of Units In Package 2 | 12 |
| Package 2 Height | 30 cm |
| Package 2 Width | 30 cm |
| Package 2 Length | 40 cm |
| Package 2 Weight | 9713 g |
| Unit Type Of Package 3 | P12 |
| Number Of Units In Package 3 | 288 |
| Package 3 Height | 95 cm |
| Package 3 Width | 80 cm |
| Package 3 Length | 120 cm |
| Package 3 Weight | 242112 g |



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |


TM200CE40T

Dimensions Drawings

Dimensions Drawings

Dimensions







Mounting and Clearance

Mounting and Clearance

Mounting on a Rail




Direct Mounting on a Panel Surface




Mounting Position

TM200CE40T



TM200CE40T












Clearance





TMCR2•••Installation




TM200CE40T










TMCR2 ••• De-Installation








TM200CE40T




Connections and Schema

Wiring Diagram / Connections Schema


DC Power Supply



Digital Inputs (Sink or Source)




(**) 10...17



- (*) Type T fuse
- (**) Fast inputs
- A Sink wiring (positive logic)
- B Source wiring (negative logic)
- (1) The COM0 and COM1 terminals are **not** connected internally.

Regular and Fast Transistor Output



** Q0...Q3




- (*) Type T fuse
- (**) Fast outputs
- (1) The V0+, V1+ and V2+ terminals are not connected internally.


TM200CE40T

(2) The V0-, V1- and V2- terminals are not connected internally.

USB Mini-B Connection



SL1 Connection



Ethernet Connection

