



# module TM3 - 4 analog inputs spring

TM3AI4G

## Main

Range Of Product	Modicon TM3  Analog input module	
Product Or Component Type		
Range Compatibility	Modicon M221	
. ,	Modicon M241	
	Modicon M251	
	Modicon M262	
Analogue Input Number	4	
Analogue Input Type	current 420 mA	
	current 020 mA	
	voltage 010 V	
	voltage - 1010 V	

## Complementary

Analogue Input Resolution	12 bits
-	11 bits + sign
	•
Permissible Continuous Overload	13 V, analogue input type: voltage
	40 mA, analogue input type: current
Input Impedance	<= 50 Ohm current
	>= 1 MOhm voltage
Lsb Value	2.44 mV 010 Vvoltage
	4.88 mV - 1010 Vvoltage
	4.88 μA 020 mAcurrent
	3.91 µA 420 mAcurrent
Conversion Time	1 ms + 1 ms per channel + 1 controller cycle time
Sampling Duration	1 ms
Absolute Accuracy Error	+/- 0.1 % of full scale at 25 °C
	+/- 1 % of full scale
Temperature Drift	+/- 0.006 %FS/°C
Repeat Accuracy	+/-0.5 %FS
Non-Linearity	+/- 0.01 %FS
Cross Talk	<= 1 LSB
[Us] Rated Supply Voltage	24 V DC
Supply Voltage Limits	20.428.8 V
Type Of Cable	Twisted shielded pairs cable <30 m for input circuit
Current Consumption	35 mA at 5 V DC via bus connector no load
	45 mA at 5 V DC via bus connector full load
	30 mA at 24 V DC via external supply
Local Signalling	1 LED (green) for PWR

Electrical Connection	10 x 1.5 mm² removable spring terminal block with pitch 3.81 mm adjustment for inputs and supply 10 x 1.5 mm² removable spring terminal block with pitch 3.81 mm adjustment for inputs	
Insulation	Between input and supply at 1500 V AC Between input and internal logic at 500 V AC	
Marking	CE	
Surge Withstand	1 kV power supply common mode conforming to IEC 61000-4-5 0.5 kV power supply differential mode conforming to IEC 61000-4-5 1 kV input common mode conforming to IEC 61000-4-5	
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 plate or panel with fixing kit	
Height	90 mm	
Depth	70 mm	
Width	23.6 mm	
Net Weight	0.1 kg	

## **Environment**

Standards	IEC 61131-2	
Product Certifications	CE UKCA RCM EAC cULus cULus HazLoc	
Resistance To Electrostatic Discharge	8 kV in air conforming to IEC 61000-4-2 4 kV on contact conforming to IEC 61000-4-2	
Resistance To Electromagnetic 10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3 3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3 1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3		
Resistance To Magnetic Fields	30 A/m conforming to IEC 61000-4-8	
esistance To Fast Transients 1 kV (I/O) conforming to IEC 61000-4-4		
Resistance To Conducted Disturbances	10 V 0.1580 MHz conforming to IEC 61000-4-6 3 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to Marine specification (LR, ABS, DNV, GL)	
ectromagnetic Emission  Radiated emissions - test level: 40 dBµV/m QP class A ( 10 m) at 302 conforming to IEC 55011  Radiated emissions - test level: 47 dBµV/m QP class A ( 10 m) at 230 conforming to IEC 55011		
Immunity To Microbreaks	10 ms	
Ambient Air Temperature For Operation	-1055 °C horizontal installation -1035 °C vertical installation	
Ambient Air Temperature For Storage	-2570 °C	
Relative Humidity	1095 %, without condensation (in operation) 1095 %, without condensation (in storage)	
Ip Degree Of Protection IP20		
Pollution Degree	2	
Operating Altitude	02000 m	
Storage Altitude	03000 m	
Vibration Resistance	3.5 mm at 58.4 Hz on DIN rail 3 gn at 8.4150 Hz on DIN rail	

Shock Resistance 15 gn for 11 ms

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	12.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	195.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	9
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2.292 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	288
Package 3 Height	80 cm
Package 3 Width	105 cm
Package 3 Length	125 cm
Package 3 Weight	91.24 kg



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance


<b>⊘</b>	Toxic Heavy Metal Free	
	Mercury Free	
<b>②</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

## **Dimensions Drawings**

#### **Dimensions**




(\*) 8.5 mm/0.33 in when the clamp is pulled out.


## TM3AI4G

## Mounting and Clearance


## **Spacing Requirements**




## Mounting on a Rail



## **Incorrect Mounting**





#### Mounting on a Panel Surface



(1) Install a mounting strip

## **Mounting Hole Layout**






Connections and Schema

## Analogue Input Module

#### Wiring Diagram (Current / Voltage)



- (\*) Type T fuse
- (1) Current/Voltage analog output device