



module TM3 - 4 analog outputs spring

TM3AQ4G

Main

Range Of Product	Modicon TM3	
Product Or Component Type	Analog output module	
Range Compatibility	Modicon M221	
	Modicon M241	
	Modicon M251	
	Modicon M262	
Analogue Output Number	4	
Analogue Output Type	Current: 420 mA	
	Current: 020 mA	
	Voltage: 010 V	
	Voltage: - 1010 V	

Complementary

Analogue Input Resolution	12 bits 11 bits + sign
Analogue Output Resolution	12 bits 11 bits + sign
Lsb Value	2.44 mV 010 Vvoltage 4.88 mV - 1010 Vvoltage 4.88 μA 020 mAcurrent 3.91 μA 420 mAcurrent
Load Type	Resistive
Load Impedance Ohmic	1 kOhm voltage 300 Ohm current
Stabilisation Time	1 ms
Conversion Time	1 ms + 1 ms per channel + 1 controller cycle time
Absolute Accuracy Error	+/- 1 % of full scale +/- 0.2 % of full scale at 25 °C
Temperature Drift	+/- 0.01 %FS/°C
Repeat Accuracy	+/- 0.4 %FS
Non-Linearity	+/- 0.2 %FS
Output Ripple	20 mV
Cross Talk	<= 1 LSB
[Us] Rated Supply Voltage	24 V DC
Supply Voltage Limits	20.428.8 V
Type Of Cable	Twisted shielded pairs cable <30 m for output circuit

Current Consumption	40 mA at 5 V DC via bus connector no load 50 mA at 5 V DC via bus connector full load 50 mA at 24 V DC via external supply no load 125 mA at 24 V DC via external supply full load	
Local Signalling	1 LED (green) for PWR	
Electrical Connection	11 x 2.5 mm² removable spring terminal block with pitch 5.08 mm adjustment for outputs and supply	
Insulation	Between output and supply at 1500 V AC Between output and internal logic at 500 V AC	
Marking	CE	
Surge Withstand	1 kV power supply common mode conforming to IEC 61000-4-5 0.5 kV power supply differential mode conforming to IEC 61000-4-5 1 kV output common mode conforming to IEC 61000-4-5	
Mounting Support	Support Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 plate or panel with fixing kit	
Height	90 mm	
Depth	70 mm	
Width	23.6 mm	
Net Weight	0.1 kg	

Environment

Standards	IEC 61131-2
Product Certifications	CE UKCA RCM EAC cULus cULus
Resistance To Electrostatic Discharge	8 kV in air conforming to IEC 61000-4-2 4 kV on contact conforming to IEC 61000-4-2
Resistance To Electromagnetic Fields	10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3 3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3 1 V/m 2 GHz3 GHz conforming to IEC 61000-4-3
Resistance To Magnetic Fields 30 A/m conforming to IEC 61000-4-8	
Resistance To Fast Transients 1 kV (I/O) conforming to IEC 61000-4-4	
Resistance To Conducted Disturbances 10 V 0.1580 MHz conforming to IEC 61000-4-6 3 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming Marine specification (LR, ABS, DNV, GL)	
Electromagnetic Emission	Radiated emissions - test level: 40 dBμV/m QP class A (10 m) at 30230 MHz conforming to IEC 55011 Radiated emissions - test level: 47 dBμV/m QP class A (10 m) at 2301000 MHz conforming to IEC 55011
Immunity To Microbreaks	10 ms
Ambient Air Temperature For Operation	-1055 °C horizontal installation -1035 °C vertical installation
Ambient Air Temperature For Storage	-2570 °C
Relative Humidity	1095 %, without condensation (in operation) 1095 %, without condensation (in storage)
Ip Degree Of Protection	IP20
Pollution Degree	2
Operating Altitude 02000 m	

Storage Altitude	03000 m
Vibration Resistance	3.5 mm at 58.4 Hz on DIN rail 3 gn at 8.4150 Hz on DIN rail
Shock Resistance	15 gn for 11 ms

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.5 cm
Package 1 Width	12.5 cm
Package 1 Length	10.5 cm
Package 1 Weight	200.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	9
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2.316 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	288
Package 3 Height	75 cm
Package 3 Width	120 cm
Package 3 Length	80 cm
Package 3 Weight	83 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Toxic Heavy Metal Free	
	Mercury Free	
②	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings

Dimensions




(*) 8.5 mm/0.33 in when the clamp is pulled out.


TM3AQ4G

Mounting and Clearance

Spacing Requirements




Mounting on a Rail



Incorrect Mounting





Mounting on a Panel Surface



(1) Install a mounting strip

Mounting Hole Layout






TM3AQ4G

Connections and Schema

Analogue Output Module

Wiring Diagram (Current / Voltage)



- (*) Type T fuse
- (1) Voltage/current pre-actuator