Specifications





## analog output module - 2O - +/-10 V/0..20 mA - 12 bits

TM5SAO2L

### Main

Range Of Product	Modicon TM5		
Product Or Component Type	Analog output module		
Analogue Output Number	2		
Analogue Output Resolution	12 bits + sign, +/- 10 V 12 bits, 020 mA		

## Complementary

Complementary					
Range Compatibility	Modicon LMC058 Modicon M258				
Product Compatibility	Motion controller Logic controller				
Analogue Output Type	Current 020 mA Voltage +/- 10 V				
Measurement Resolution	4.882 mV, +/- 10 V 9.766 μA, 020 mA				
Colour	White				
Response Time	<= 1 ms				
Minimum Output Impedance	1 Ohm				
Load Impedance Ohmic	<= 500 Ohm (current)				
Sampling Duration	200 µs				
Measurement Error	< 0.15 % of full scale +/- 10 V at 25 °C < 0.15 % of full scale 020 mA at 25 °C				
Temperature Coefficient	0.02 %FS/°C, analogue output type: current 0.02 %FS/°C, analogue output type: voltage				
Non-Linearity	< 0.007 %FS, analogue output type: current < 0.007 %FS, analogue output type: voltage				
Type Of Cable	Shielded cable				
Isolation	500 Vrms AC insulation between channel and bus No insulation between channels				
Supply	Internal				
[Us] Rated Supply Voltage	24 V DC -1520 %				
Local Signalling	1 LED green for power supply 1 LED red for power supply 2 LEDs yellow for output status				
Current Consumption	2 mA at 5 V DC bus 46 mA at 24 V DC input/output				
Maximum Power Dissipation In W	1.11 W				

Marking	CE
Net Weight	0.025 kg

### Environment

Environment					
Standards	CSA C22.2 No 142 IEC 61131-2 UL 508 CSA C22.2 No 213				
Product Certifications	CSA GOST-R cULus C-Tick				
Ambient Air Temperature For Operation	055 °C without derating (horizontal installation) 060 °C with derating factor (horizontal installation) 050 °C (vertical installation)				
Ambient Air Temperature For Storage	-2570 °C				
Relative Humidity	595 % without condensation				
Ip Degree Of Protection	IP20 conforming to IEC 61131-2				
Pollution Degree	2 conforming to IEC 60664				
Operating Altitude	02000 m				
Storage Altitude	03000 m				
Vibration Resistance	1 gn at 8.4150 Hz on DIN rail 3.5 mm at 58.4 Hz on DIN rail				
Shock Resistance	15 gn for 11 ms				
Resistance To Electrostatic Discharge	4 kV on contact conforming to IEC 61000-4-2 8 kV in air conforming to IEC 61000-4-2				
Resistance To Electromagnetic Fields	1 V/m 22.7 GHz conforming to IEC 61000-4-3 10 V/m 802000 MHz conforming to IEC 61000-4-3				
Resistance To Fast Transients	1 kV (I/O) conforming to IEC 61000-4-4 1 kV (shielded cable) conforming to IEC 61000-4-4 2 kV (power lines) conforming to IEC 61000-4-4				
Surge Withstand	0.5 kV differential mode conforming to IEC 61000-4-5 1 kV common mode conforming to IEC 61000-4-5				
Electromagnetic Compatibility	EN/IEC 61000-4-6				
Disturbance Radiated/Conducted	CISPR 11				

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	6.000 cm
Package 1 Length	10.500 cm
Package 1 Weight	39.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	97
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm

Package 2 Weight

3.996 kg

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

### **Certifications & Standards**

Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins			
Circularity Profile	End of Life Information			

**Dimensions Drawings** 

#### TM5 Slice

#### Dimensions


mm in. 75 2.95 0.49 0.49 0.60 60 60 60

TM5SAO2L


Mounting and Clearance

#### TM5 System

#### **Spacing Requirements**



#### Mounting on a DIN Rail



Connections and Schema


#### TM5 System Wiring Recommendations

#### Wire Sizes to Use with the Removable Spring Terminal Blocks

mm in. ō	9 .35		å		æ
	mm <sup>2</sup>	0,082,5	0,252,5	0,251,5	2 x 0,252 x 0,75
	AWG	2814	2414	2416	2 x 242 x 18

#### Electronic Module 2AO ±10V/0-20mA 12 Bits

#### Wiring Diagram



(1) Internal electronics

(2) 24 Vdc I/O power segment integrated into the bus bases

(I) Current

(U) Voltage