

Product datasheet

Specifications



cartridge M200 - 2 temperature inputs - I/O extension

TMCR2TI2

Main

Range Of Product	Easy Modicon M200
Product Or Component Type	Analogue input cartridge
Product Compatibility	Easy Modicon M200
Analogue Input Number	2

Complementary

Analogue Input Type	thermocouple - 200...1000 °C with thermocouple J thermocouple - 200...1300 °C with thermocouple K thermocouple 0...1760 °C with thermocouple R thermocouple 0...1760 °C with thermocouple S thermocouple 0...1820 °C with thermocouple B thermocouple - 200...400 °C with thermocouple T thermocouple - 200...1300 °C with thermocouple N thermocouple - 200...800 °C with thermocouple E thermocouple 0...2315 °C with thermocouple C Ni 100/Ni 1000 temperature probe - 60...180 °C Pt 100 temperature probe - 200...850 °C Pt 1000 temperature probe - 200...600 °C
Analogue Input Resolution	14 bits
LSb Value	0.1 °C
Sampling Duration	125 ms, analogue input type: thermocouple 250 ms, analogue input type: temperature probe
Absolute Accuracy Error	+/- 0.1 % of full scale at 25 °C for Pt 100/Pt 1000, Ni 100/ Ni 1000 temperature probe +/- 0.4 % of full scale at 25 °C for thermocouple K - 200...0 °C +/- 0.1 % of full scale at 25 °C for thermocouple K 0...1300 °C +/- 0.4 % of full scale at 25 °C for thermocouple J - 200...0 °C +/- 0.1 % of full scale at 25 °C for thermocouple J 0...1000 °C +/- 0.4 % of full scale at 25 °C for thermocouple E - 200...0 °C +/- 0.1 % of full scale at 25 °C for thermocouple E 0...800 °C +/- 0.4 % of full scale at 25 °C for thermocouple T - 200...0 °C +/- 0.1 % of full scale at 25 °C for thermocouple T 0...400 °C +/- 0.4 % of full scale at 25 °C for thermocouple N - 200...0 °C +/- 0.1 % of full scale at 25 °C for thermocouple N 0...1300 °C +/- 0.1 % of full scale for thermocouple C
Temperature Drift	+/- 0.02 %FS/°C
Repeat Accuracy	+/- 0.5 %FS
Non-Linearity	+/- 0.01 %FS
Cross Talk	<= 1 LSB
Type Of Cable	Twisted shielded pairs cable
Electrical Connection	3 x 1.5 mm² 2 screw terminal blocks with pitch 3.81 mm adjustment for inputs
Maximum Cable Distance Between Devices	Twisted shielded pairs cable: <30 m for input
Insulation	Non-insulated between analogue input and internal logic

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	41 mm
Depth	15 mm
Width	35 mm
Net Weight	0.012 kg
Input Impedance	>= 1 MOhm

Environment

Immunity To Microbreaks	10 ms
-------------------------	-------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	4.800 cm
Package 1 Length	7.000 cm
Package 1 Weight	33.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	75
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	2.735 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	1200
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	51.760 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

✓ Toxic Heavy Metal Free	
✓ Mercury Free	
✓ Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration