Product datasheet





Complete body contact assembly, Harmony XB4, Single contact, with body fixing collar, metal, spring clamp terminal, 2NC

ZB4BZ1045

Main

Range Of Product	Harmony XB4	
Product Or Component Type	pe Complete body/contact assembly	
Device Short Name	ZB4	
Fixing Collar Material	Zamak	
Sale Per Indivisible Quantity	1	
Head Type	Standard	
Contacts Type And Composition	2 NC	
Contact Operation	Slow-break	
Contact Block Type	Single	
Device Composition	Fixing collar Body	
Connections - Terminals	Spring clamp terminals	

Complementary

Cad Overall Width	46.2 mm	
Cad Overall Height	27.6 mm	
Cad Overall Depth	30 mm	
Terminals Description Iso N°1	(11-12)NC	
Net Weight	0.054 kg	
Contacts Usage	Standard contacts	
Positive Opening	With conforming to IEC 60947-5-1 appendix K	
Operating Travel	1.5 mm (NC changing electrical state) 4.3 mm (total travel)	
Mechanical Durability	urability 10000000 cycles	
Contacts Material	cts Material Silver alloy (Ag/Ni)	
Electrical Durability	ectrical Durability 10000000 cycles	

Environment

Protective Treatment	тн
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-4070 °C
Ip Degree Of Protection	IP20 conforming to IEC 60529

Life Is On Schneider 10 May 2024

Standards	IEC 60947-1 IEC 60947-5-5 CSA C22.2 No 14 IEC 60947-5-4 IEC 60947-5-1 JIS C8201-5-1 UL 508 JIS C8201-1	
Product Certifications	UL BV CSA GL LROS (Lloyds register of shipping) DNV	
Vibration Resistance	istance 5 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock Resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	3.8 cm
Package 1 Length	4.6 cm
Package 1 Weight	61.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	200
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	12.712 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


②	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings

Dimensions



ZB4BZ1045

Mounting and Clearance


Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connectors or on Printed Circuit Board

(1)

(2)

Connection by Screw Clamp Terminals or Plug-in



Connection by Faston Connectors

(1) Diameter on finished panel or support

(3)

- (2) 40 mm min. / 1.57 in. min.
- (3) 30 mm min. / 1.18 in. min.
- (4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm $_0^{+0.4}$ / 0.88 in. $_0^{+0.016}$)

(4)

- (5) 45 mm min. / 1.78 in. min.
- (6) 32 mm min. / 1.26 in. min.