# **Product datasheet**

Specifications





### TeSys D contactor - 3P - <= 440 V - 65 A AC-3 - 100...250 V AC/DC

coil

Local distributor code: 407811889

LC1D65AKUE

#### EAN Code: 3606480988288

#### Main

Range	TeSys TeSys Deca
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Motor control Resistive load
Utilisation Category	AC-1 AC-3 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz
[le] Rated Operational Current	80 A (at <60 °C) at <= 440 V AC-1 for power circuit 65 A (at <60 °C) at <= 440 V AC-3 for power circuit 65 A (at <60 °C) at <= 440 V AC-3e for power circuit
[Uc] Control Circuit Voltage	100250 V AC 50/60 Hz 100250 V DC

#### Complementary

18.5 kW at 220230 V AC 50 Hz (AC-3)
30 kW at 380400 V AC 50 Hz (AC-3)
37 kW at 415 V AC 50 Hz (AC-3)
37 kW at 440 V AC 50 Hz (AC-3)
37 kW at 500 V AC 50 Hz (AC-3)
37 kW at 660690 V AC 50 Hz (AC-3)
18.5 kW at 220230 V AC 50 Hz (AC-3e)
30 kW at 380400 V AC 50 Hz (AC-3e)
37 kW at 415 V AC 50 Hz (AC-3e)
37 kW at 440 V AC 50 Hz (AC-3e)
37 kW at 500 V AC 50 Hz (AC-3e)
37 kW at 660690 V AC 50 Hz (AC-3e)
5 hp at 115 V AC 60 Hz for 1 phase motors
10 hp at 230/240 V AC 60 Hz for 1 phase motors
20 hp at 200/208 V AC 60 Hz for 3 phases motors
20 hp at 230/240 V AC 60 Hz for 3 phases motors
40 hp at 460/480 V AC 60 Hz for 3 phases motors
50 hp at 575/600 V AC 60 Hz for 3 phases motors
LC1D
3 NO
With
80 A (at 60 °C) for power circuit
10 A (at 60 °C) for signalling circuit

Irms Rated Making Capacity	1000 A at 440 V for power circuit conforming to IEC 60947
	140 A AC for signalling circuit conforming to IEC 60947-5-1
	250 A DC for signalling circuit conforming to IEC 60947-5-1
Potod Brooking Consoity	
Rated Breaking Capacity	1000 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand	110 A 40 °C - 10 min for power circuit
Current	260 A 40 °C - 1 min for power circuit
	640 A 40 °C - 10 s for power circuit
	900 A 40 °C - 1 s for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	125 A gG at <= 690 V coordination type 1 for power circuit
_	125 A gG at <= 690 V coordination type 2 for power circuit
	10 A gG for signalling circuit conforming to IEC 60947-5-1
Average Impedance	1.5 mOhm - Ith 80 A 50 Hz for power circuit
Power Dissipation Per Pole	9.6 W AC-1
	6.3 W AC-1
	6.3 W AC-3 6.3 W AC-3e
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1
	Signalling circuit: 690 V conforming to IEC 60947-1
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	6 Mcycles
Electrical Durability	1.8 Movelog 57 A AC 3 of $10.5 = 140.1$
	1.8 Mcycles 57 A AC-3 at Ue <= 440 V
	0.5 Mcycles 80 A AC-1 at Ue <= 440 V
	1.8 Mcycles 57 A AC-3e at Ue <= 440 V
Control Circuit Type	AC/DC at 50/60 Hz AC/DC electronic
Coil Technology	Built-in bidirectional peak limiting
Control Circuit Voltago Limita	
Control Circuit Voltage Limits	<= 0.1 Uc (-4070 °C):drop-out AC/DC
	0.851.1 Uc (-4060 °C):operational AC/DC
	11.1 Uc (6070 °C):operational AC/DC
Inrush Power In Va	18 VA 50/60 Hz (at 20 °C)
Inrush Power In W	14 W (at 20 °C)
Hold-In Power Consumption In Va	1.8 VA 50/60 Hz (at 20 °C)
Hold-In Power Consumption In W	1.2 W at 20 °C
Heat Dissipation	1.2 W at 50/60 Hz
Operating Time	5565 ms closing
	20120 ms opening (date code >= 17221)
	2080 ms opening (date code >= $1221$ ) 2080 ms opening (date code >= $18011$ )
	20ou mo opening (date code >= 10011)
Maximum Operating Rate	3600 cyc/h 60 °C

Connections - Terminals	Control circuit: screw clamp terminals 1 14 mm <sup>2</sup> - cable stiffness: flexible without
	cable end
	Control circuit: screw clamp terminals 2 14 mm <sup>2</sup> - cable stiffness: flexible without
	cable end
	Control circuit: screw clamp terminals 1 14 mm <sup>2</sup> - cable stiffness: flexible with cable end
	Control circuit: screw clamp terminals 2 12.5 mm <sup>2</sup> - cable stiffness: flexible with
	cable end
	Control circuit: screw clamp terminals 1 14 mm <sup>2</sup> - cable stiffness: solid
	Control circuit: screw clamp terminals 2 14 mm <sup>2</sup> - cable stiffness: solid
	Power circuit: EverLink BTR screw connectors 1 135 mm <sup>2</sup> - cable stiffness: flexible without cable end
	Power circuit: EverLink BTR screw connectors 1 135 mm <sup>2</sup> - cable stiffness: flexible with cable end
	Power circuit: EverLink BTR screw connectors 1 135 mm <sup>2</sup> - cable stiffness: solid
	Power circuit: EverLink BTR screw connectors 2 125 mm <sup>2</sup> - cable stiffness: flexible without cable end
	Power circuit: EverLink BTR screw connectors 2 125 mm <sup>2</sup> - cable stiffness: flexible
	with cable end
	Power circuit: EverLink BTR screw connectors 2 125 mm <sup>2</sup> - cable stiffness: solid
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm
	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2
	Power circuit: 8 N.m - on EverLink BTR screw connectors - cable 2535 mm <sup>2</sup>
	hexagonal screw head 4 mm
	Power circuit: 5 N.m - on EverLink BTR screw connectors - cable 125 mm <sup>2</sup>
	hexagonal screw head 4 mm
	Power circuit: 5 N.m - with screwdriver pozidriv No 2
	Control circuit: 1.7 N.m - with screwdriver pozidriv No 2
Auxiliary Contact Composition	1 NO + 1 NC
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1
	type mirror contact 1 NC conforming to IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Voltage	17 V for signalling circuit
Minimum Switching Current	5 mA for signalling circuit
Insulation Resistance	> 10 MOhm for signalling circuit
	1.5 ma on do anaraiastian batwan NC and NO contact
Non-Overlap Time	
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Non-Overlap Time Mounting Support	•

### Environment

Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 IEC 60335-1
Product Certifications	CCC CSA EAC UL KC DNV-GL LROS (Lloyds register of shipping) UKCA
Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Climatic Withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating
Operating Altitude	03000 m
Fire Resistance	850 °C conforming to IEC 60695-2-1

Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor open (10 Gn for 11 ms) Shocks contactor closed (15 Gn for 11 ms)	
Height	122 mm	
Width	55 mm	
Depth	120 mm	
Net Weight	1.002 kg	

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	13.800 cm
Package 1 Length	15.200 cm
Package 1 Weight	1.055 kg
Unit Type Of Package 2	S02
Number Of Units In Package 2	9
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.797 kg

## Contractual warranty

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

 Mercury Free
 Rohs Exemption Information Yes
 Halogen Free Plastic Parts & Cables Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information