Product datasheet

Specifications





module XPSAXE - stop and switch monitoring - 24 V DC/AC

XPSAXE5120C

() Discontinued on: 16 Jan 2024

Main

Range Of Product	Preventa Safety automation
Product Or Component Type	Preventa safety module
Safety Module Name	XPSAXE
Safety Module Application	For emergency stop and switch monitoring
Safety Level	Can reach PL e/category 4 conforming to EN/ISO 13849-1 Can reach SILCL 3 conforming to EN/IEC 62061
Safety Reliability Data	DC > 99 % conforming to EN/ISO 13849-1 MTTFd = 457 years conforming to EN/ISO 13849-1 PFHd = 3E-8 1/h conforming to EN/IEC 62061
Connections - Terminals	Spring terminals, removable terminal block, 1 x 0.21 x 2.5 mm ² solid without cable end Spring terminals, removable terminal block, 1 x 0.21 x 2.5 mm ² flexible without cable end Spring terminals, removable terminal block, 1 x 0.251 x 2.5 mm ² flexible with cable end, without bezel Spring terminals, removable terminal block, 1 x 0.251 x 2.5 mm ² flexible with cable end, with bezel Spring terminals, removable terminal block, 2 x 0.52 x 1 mm ² flexible with cable end, with double bezel Spring terminals, removable terminal block, 2 x 0.52 x 1 mm ² flexible with cable end, with double bezel Spring terminals, removable terminal block
Output Type	Relay instantaneous opening, 3 NO circuit(s), volt-free
Number Of Additional Circuits	1 NC
[Us] Rated Supply Voltage	24 V DC - 1510 % 24 V AC

Complementary

Synchronisation Time Between Inputs	< 0.5 s
Supply Frequency	50/60 Hz
Maximum Power Consumption In Va	4 VA DC
[Uc] Control Circuit Voltage	24 V DC
Breaking Capacity	3600 VA inrush AC-15 B300 relay output 360 VA holding AC-15 B300 relay output
Breaking Capacity	1.5 A at 24 V (DC-13) time constant: 50 ms for relay output
Output Thermal Current	6 A for instantaneous and time delay outputs
Associated Fuse Rating	6 A gG for instantaneous outputs
Minimum Output Current	10 mA for relay output
Minimum Output Voltage	17 V for relay output

Maximum Response Time On Input Open	80 ms
[Ui] Rated Insulation Voltage	300 V (pollution degree 2) conforming to IEC 60947-5-1 300 V (pollution degree 2) conforming to DIN VDE 0110 part 1
[Uimp] Rated Impulse Withstand Voltage	4 kV overvoltage category III conforming to IEC 60947-5-1 4 kV overvoltage category III conforming to DIN VDE 0110 part 1
Local Signalling	2 LEDs
Mounting Support	35 mm symmetrical DIN rail
Net Weight	0.229 kg

Environment

Standards	EN/ISO 13850 EN 1088/ISO 14119 EN/IEC 60204-1 EN/IEC 60947-5-1
Product Certifications	BG CSA UL
Ip Degree Of Protection	IP20 conforming to EN/IEC 60529 IP40 conforming to EN/IEC 60529
Ambient Air Temperature For Operation	-2555 °C
Ambient Air Temperature For Storage	-2575 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	11.5 cm
Package 1 Length	12.0 cm
Package 1 Weight	203.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	20
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.376 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information