



module XPSAXE - stop and switch monitoring - 24 V DC/AC

XPSAXE5120P

! Discontinued on: 16 Jan 2024



Main

Range Of Product	Preventa Safety automation	
Product Or Component Type	Preventa safety module	
Safety Module Name	XPSAXE	
Safety Module Application For emergency stop and switch monitoring		
Safety Level	Can reach PL e/category 4 conforming to EN/ISO 13849-1	
	Can reach SILCL 3 conforming to EN/IEC 62061	
Safety Reliability Data	DC > 99 % conforming to EN/ISO 13849-1	
	MTTFd = 457 years conforming to EN/ISO 13849-1	
	PFHd = 3E-8 1/h conforming to EN/IEC 62061	
Connections - Terminals	Captive screw clamp terminals, removable terminal block, 2 x 0.52 x 1.5 mm²	
	flexible with cable end, with double bezel	
	Captive screw clamp terminals, removable terminal block, 1 x 0.21 x 2.5 mm ² solid without cable end	
	Captive screw clamp terminals, removable terminal block, 1 x 0.21 x 2.5 mm ² flexible without cable end	
	Captive screw clamp terminals, removable terminal block, 1 x 0.251 x 2.5 mm ² flexible with cable end, without bezel	
	Captive screw clamp terminals, removable terminal block, 1 x 0.251 x 1.5 mm ² flexible with cable end, with bezel	
	Captive screw clamp terminals, removable terminal block, 2 x 0.22 x 1 mm² solid without cable end	
	Captive screw clamp terminals, removable terminal block, 2 x 0.22 x 1 mm² flexible without cable end	
	Captive screw clamp terminals, removable terminal block, 2 x 0.252 x 1 mm ²	
	flexible with cable end, without bezel	
Output Type	Relay instantaneous opening, 3 NO circuit(s), volt-free	
Number Of Additional Circuits	1 NC	
[Us] Rated Supply Voltage	24 V DC - 1510 %	
	24 V AC	

Complementary

17 May 2024

Synchronisation Time Between Inputs	< 0.5 s	
Supply Frequency	50/60 Hz	
Maximum Power Consumption In Va	4 VA DC	
[Uc] Control Circuit Voltage	24 V DC	
Breaking Capacity	3600 VA inrush AC-15 B300 relay output 360 VA holding AC-15 B300 relay output	
Breaking Capacity	1.5 A at 24 V (DC-13) time constant: 50 ms for relay output	
Output Thermal Current	6 A for instantaneous and time delay outputs	
Associated Fuse Rating	ciated Fuse Rating 6 A gG for instantaneous outputs	

Minimum Output Current	10 mA for relay output	
Minimum Output Voltage	17 V for relay output	
Maximum Response Time On Input Open	80 ms	
[Ui] Rated Insulation Voltage	300 V (pollution degree 2) conforming to IEC 60947-5-1 300 V (pollution degree 2) conforming to DIN VDE 0110 part 1	
[Uimp] Rated Impulse Withstand Voltage	4 kV overvoltage category III conforming to IEC 60947-5-1 4 kV overvoltage category III conforming to DIN VDE 0110 part 1	
Local Signalling	2 LEDs	
Mounting Support	35 mm symmetrical DIN rail	
Net Weight	0.229 kg	

Environment

Standards	EN/IEC 60947-5-1 EN/IEC 60204-1 EN/ISO 13850 EN 1088/ISO 14119
Product Certifications	UL BG CSA
Ip Degree Of Protection	IP20 conforming to EN/IEC 60529 IP40 conforming to EN/IEC 60529
Ambient Air Temperature For Operation	-2555 °C
Ambient Air Temperature For Storage	-2575 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.0 cm
Package 1 Width	11.5 cm
Package 1 Length	12.5 cm
Package 1 Weight	211.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	20
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.584 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Toxic Heavy Metal Free	
②	Mercury Free	
②	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information