Specifications





Modular tower lights, Harmony XVM, aluminium, red orange green, 45mm, steady, incandescent bulb BA 15d, with buzzer, 24V AC DC

XVMB1RAGS

### Main

Range Of Product	Harmony XVM	
Product Or Component Type	Pre-assembled and pre-cabled indicator bank	
Beacon Or Indicator Bank Unit Type	3 illuminated units	
Component Name	XVM	
Light Source	Orange incandescent bulb with BA 15d base steady signalling <5 W Green incandescent bulb with BA 15d base steady signalling <5 W Red incandescent bulb with BA 15d base steady signalling <5 W	
Light Block Color	Red/orange/green	
[Us] Rated Supply Voltage	24 V AC/DC	
Indicator Bank Base Type	Base with integrated buzzer	
Mounting Mode	Vertical	

## Complementary

Kit Composition	Cover Plastic fixing plate Aluminium support tube Base unit		
Mounting Diameter	45 mm		
Connections - Terminals	Flying leads,clamping capacity: 1 x 0.325 mm² (AWG 22)		
Marking	CE		
Mounting Support	Aluminium tube		
[Ui] Rated Insulation Voltage	250 V conforming to IEC 60947-1		
Nominal Voltage Limit	0.851.1 Un conforming to IEC 60947-5-1		
Current Consumption	15 mA on base unit		
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60947-1		
Fundamental Frequency	4 kHz		
Net Weight	0.449 kg		

### Environment

Ip Degree Of Protection	IP42 vertical position conforming to IEC 60529	
Product Certifications	ссс	
Standards	IEC 60947-5-1 IEC 60947-1	

Ambient Air Temperature For Storage	-2570 °C
Ambient Air Temperature For Operation	-1050 °C
Overvoltage Category	Class I conforming to IEC 60947-1 Class I conforming to IEC 60947-5-1 Class I conforming to IEC 61140
Protective Treatment	TC
Noise Level	080 dB at 1 m

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	9.2 cm
Package 1 Length	55.0 cm
Package 1 Weight	565.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	20
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	12.502 kg

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Mercury Free

Rohs Exemption Information
Yes

### **Certifications & Standards**


Circularity Profile	No need of specific recycling operations	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Environmental Disclosure	Product Environmental Profile	
China Rohs Regulation	China RoHS declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
Reach Regulation	REACh Declaration	

#### **Dimensions Drawings**

#### Pre-Assembled and Pre-Cabled Tower Light with Fixing Base for Mounting on Vertical Support (Support Tube + Metal Bracket)

#### Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b2** dimension.



(1) Base unit with or without buzzer.

Number of illuminated units	b2 in mm	b2 in in.
1 unit	383	15.08
2 units	448	17.64
3 units	513	20.20
4 units	578	22.76

4

#### Connections and Schema

#### Pre-Assembled and Pre-Cabled Tower Light

#### Wire Colors


4th illuminated unit: yellow wire 3rd illuminated unit: green wire 2nd illuminated unit: white wire 1st illuminated unit: blue wire Common: black wire Buzzer (if integrated in base unit): grey wire

#### **Technical Description**

#### Base Unit with Integral Buzzer

#### Adjustment of Audible Signal

View from above:



- (1) Volume adjustment potentiometer: 0 to 85 dB. Use either a cross headed or flat tipped screwdriver.
- (2) 2-position selector for type of audible signal: continuous tone or intermittent tone