

Product datasheet

Specifications



Remote control, Harmony eXLhoist, standard, display, 6 motion push buttons, 6 auxiliary push buttons

ZART12D

Main

Range Of Product	Harmony eXLhoist
Product Or Component Type	Hand-held remote control
Device Short Name	ZART
Control Button Type	6 configurable motion push-button 6 configurable auxiliary push-button

Complementary

Material	Enclosure: PC (polycarbonate) Enclosure: PBT (polybutylene terephthalate) Cover: PP (polypropylene) Protective cover: EPDM rubber
Function Available	Accelerometer function Vibrator function
Display Type	LCD display 34 x 42 mm
Operating Distance	50 m
Mechanical Robustness	Free fall resistance 4.5 m conforming to IEC 60068-2-27
Communication Network Type	Wireless: bluetooth low energy
Transmission Frequency	2.4 GHz
Maximum Sensing Distance	100 m in free field
Response Time	< 300 ms at full duplex
Charging Time	900 s
Autonomy	30 h
Mechanical Durability	5000000 cycles
Service Life	5 year(s)
Width	100 mm
Height	340 mm
Depth	90 mm
Net Weight	0.65 kg

Environment

Radio Agreement	FCC ARIB RSS ICASA ANATEL SRRC
-----------------	---

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP65
Nema Degree Of Protection	NEMA 4
Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-20...45 °C
Operating Altitude	0...2000 m
Storage Altitude	0...3000 m
Vibration Resistance	0.075 mm conforming to IEC 60068-2-6 (f = 10...55 Hz)
Shock Resistance	100 gn conforming to IEC 60068-2-27
Relative Humidity	0...95 % at -20...60 °C operating
Product Certifications	C-Tick CSA CE JIS KC EAC UL

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.700 cm
Package 1 Width	10.200 cm
Package 1 Length	33.700 cm
Package 1 Weight	749.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	4
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.485 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

[End of Life Information](#)

Dimensions Drawings

Dimensions

