

Product data sheet

Specifications



Metal outlet grille cut-out 95 x 90mm ext dim 120x120mm IP23

NSYCAG104X95LM

Main

Range	ClimaSys
Product	ClimaSys CA
Range Compatibility	ClimaSys ClimaSys CV
Product Or Component Type	Metal louvre plate
Accessory / Separate Part Category	Thermal management accessory
Accessory / Separate Part Destination	ClimaSys ventilation system
Mounting Location	Sides of enclosure
Fixing Mode	By screws
Device Composition	1 metal louvre

Complementary

Material	Steel
Colour	Grey (RAL 7035)
Surface Finish	Epoxy-polyester powder
Cut-Out Dimensions	95 x 104 mm
Height	120 mm external:
Width	120 mm external:
Ip Degree Of Protection	IP23

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	12.5 cm
Package 1 Length	13.0 cm
Package 1 Weight	196.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations