

Product data sheet

Specifications



frequency control relay, Harmony
Control Relays, 5A, 1CO+1CO,
120â€¦277V AC

RM35HZ21FM

Main

Range Of Product	Harmony Control Relays
Relay Type	Frequency control relays
Product Or Component Type	Frequency control relay
Relay Name	RM35HZ21FM
Relay Monitored Parameters	Overfrequency and underfrequency 50 or 60 Hz
Time Delay Type	Adjustable 0.1...10 s, +/- 10 % Tt- time delay upon fault
Switching Capacity In Va	1250 VA
Minimum Switching Current	10 mA at 5 V DC
Maximum Power Consumption In Va	6 VA AC
Measurement Range	40...70 Hz
Utilisation Category	AC-12 conforming to IEC 60947-5-1 AC-13 conforming to IEC 60947-5-1 AC-14 conforming to IEC 60947-5-1 AC-15 conforming to IEC 60947-5-1 DC-12 conforming to IEC 60947-5-1 DC-13 conforming to IEC 60947-5-1 DC-14 conforming to IEC 60947-5-1

Complementary

Reset Time	2000 ms time delay
Maximum Switching Voltage	250 V AC/DC
[Us] Rated Supply Voltage	120...277 V AC
[Un] Rated Nominal Voltage	120...277 V AC, non self-powered
Supply Voltage Limits	102...308 V AC
Control Circuit Frequency	40...70 Hz
Width	35 mm
Output Contacts	1 C/O + 1 C/O
Contacts Material	Cadmium free
Nominal Output Current	5 A
Maximum Input Frequency	70 Hz
Maximum Measuring Cycle	200 ms measurement cycle as true rms value
Delay At Power Up	0.5 s
Hysteresis	0.3 % fixed

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Measurement Accuracy	+/- 10 % of the full scale value in input +/- 10 % of the full scale value in time delay
Repeat Accuracy	+/- 0.5 % for input and measurement circuit +/- 0.5 % for time delay
Measurement Error	+/- 0.05 %/°C with temperature variation < +/- 1 % over the whole range with voltage variation
Threshold Setting	-2...10 Hz -10...2 Hz
Marking	CE : 73/23/EEC CE : EMC 89/336/EEC
Overvoltage Category	III conforming to IEC 60664-1
Insulation Resistance	> 500 MOhm at 500 V DC between supply and relay output conforming to IEC 60255-5 > 500 MOhm at 500 V DC between measurement and relay output conforming to IEC 60664-1 > 1 MOhm at 500 V DC between supply and measurement conforming to IEC 60255-5 > 500 MOhm at 500 V DC between supply and relay output conforming to IEC 60664-1 > 500 MOhm at 500 V DC between measurement and relay output conforming to IEC 60255-5 > 1 MOhm at 500 V DC between supply and measurement conforming to IEC 60664-1
[Ui] Rated Insulation Voltage	400 V conforming to IEC 60664-1
Operating Voltage Tolerance	- 15 % + 10 % Un
Supply Frequency	50/60 Hz +/- 10 %
Insulation	No galvanic insulation between supply and measurement
Operating Position	Any position without derating
Connections - Terminals	Screw terminals, 1 x 0.5...1 x 4 mm² (AWG 20...AWG 11) solid without cable end Screw terminals, 2 x 0.5...2 x 2.5 mm² (AWG 20...AWG 14) solid without cable end Screw terminals, 1 x 0.2...1 x 2.5 mm² (AWG 24...AWG 12) flexible with cable end Screw terminals, 2 x 0.2...2 x 1.5 mm² (AWG 24...AWG 16) flexible with cable end
Tightening Torque	0.6...1 N.m conforming to IEC 60947-1
Housing Material	Self-extinguishing plastic
Local Signalling	1 LED green for power ON 1 LED yellow for correct frequency (high R1) 1 LED yellow for correct frequency (low R2)
Mounting Support	35 mm symmetrical DIN rail conforming to IEC 60715
Electrical Durability	100000 cycles
Mechanical Durability	30000000 cycles
Operating Rate	<= 360 operations/hour full load
Control Type	Without test button

Environment

Immunity To Microbreaks	10 ms
Electromagnetic Compatibility	Emission standard for industrial environments conforming to IEC 61000-6-4 Emission standard for residential, commercial and light-industrial environments conforming to IEC 61000-6-3 Immunity for industrial environments conforming to NF EN/IEC 61000-6-2
Standards	IEC 60255-6 NF EN 60255-6

Product Certifications	GL UL CSA C-Tick GOST
Ambient Air Temperature For Storage	-40...70 °C
Ambient Air Temperature For Operation	-20...50 °C
Relative Humidity	95 % at 55 °C conforming to IEC 60068-2-30
Vibration Resistance	0.35 mm (f= 5...57.6 Hz) conforming to IEC 60068-2-6/IEC 60255-21-1 1 gn (f= 57.6...150 Hz) conforming to IEC 60068-2-6/IEC 60255-21-1
Shock Resistance	15 gn for 11 ms conforming to IEC 60255-21-1
Ip Degree Of Protection	IP20 (terminals) conforming to IEC 60529 IP30 (casing) conforming to IEC 60529
Pollution Degree	3 conforming to IEC 60664-1
Dielectric Test Voltage	2 kV AC 50 Hz
Non-Dissipating Shock Wave	4 kV

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.600 cm
Package 1 Width	8.000 cm
Package 1 Length	9.700 cm
Package 1 Weight	126.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	48
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	6.838 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)


Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Frequency Control Relay


Dimensions and Mounting



Connections and Schema

Frequency Control Relay


Wiring Diagram




Technical Description

Function Diagrams

Over-Frequency and Under-Frequency Control on 50 Hz or 60 Hz Supplies
Without memory ("No Memory" mode)



With memory ("Memory" mode)



Legend

- Tt Time delay after crossing of threshold from 0.1 s to 10 s
- Un Supply voltage
- F Monitored frequency
- H Hysteresis
- F> Over-frequency threshold
- F< Under-frequency threshold
- 11-12, 11-14 R1 output relay connections
- 21-22, 21-24 R2 output relay connections
- Relay status: black color = energized.

NOTE: In "Memory" mode, the relay opens after the time delay and stays in that position when crossing of the threshold is detected. The power supply voltage must be switched off to reset the product.