Product datasheet

Specification





iC60H - earth leakage circuit breaker - 1P + N - C curve - 10 A -10 mA - 240 V

Local distributor code: 396789970

A9D10810

EAN Code: 3606480558528

Main

Circuit Breaker Application	Distribution
Range	Acti9
Product Name	Acti9 iC60 RCBO
Product Or Component Type	Residual current breaker with overcurrent protection (RCBO)
Device Short Name	iC60H RCBO
Poles Description	1P + Ns
[In] Rated Current	10 A at 50 °C
Earthing System	TN
Curve Code	С
Earth-Leakage Sensitivity	10 mA
Breaking Capacity	10000 A Icn at 230/240 V AC 50/60 Hz

Complementary

Neutral Position	Left
Number Of Protected Poles	1
Device Location In System	Outgoer
Network Frequency	50 Hz
Network Type	AC
Trip Unit Technology	Thermal-magnetic
[Ue] Rated Operational Voltage	230/240 V AC 50/60 Hz
Residual Current Tripping Technology	Voltage dependent
Earth-Leakage Protection Time Delay	Instantaneous
Earth-Leakage Protection Class	Type A
[Icw] Rated Short-Time Withstand Current	Icw: 250 A during 8/20 μs impulse withstand
[Ics] Rated Service Breaking Capacity	7500 A at 230/240 V AC 50/60 Hz
Limitation Class	3
[Ui] Rated Insulation Voltage	400 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	4 kV
Surge Current	250 A
Suitability For Isolation	Yes

Contact Position Indicator	Yes	
Control Type	Toggle	
Local Signalling	ON/OFF indication	
Mounting Mode	Clip-on	
Mounting Support	DIN rail	
Comb Busbar And Distribution Block Compatibility	NO	
9 Mm Pitches	2	
Height	110 mm	
Width	18 mm	
Depth	77.5 mm	
Net Weight	205 g	
Colour	White	
Mechanical Durability	20000 cycles	
Electrical Durability	5000 cycles	
Provision For Padlocking	Padlockable with padlock Ø 4 mm	
Locking Options Description	ON/OFF locking facilities	
Connections - Terminals	Screw clamp terminal (top) 125 mm² rigid without cable end Screw clamp terminal (top) 116 mm² flexible Screw clamp terminal (bottom) 116 mm² rigid without cable end Screw clamp terminal (bottom) 110 mm² flexible	
Wire Stripping Length	Power circuit: 13 mm for bottom connection Power circuit: 14 mm for top connection	
Tightening Torque	Power circuit: 3.5 N.m top Power circuit: 2 N.m bottom	
Earth-Leakage Protection	Integrated	

Environment

Standards	AS/NZS 61009.1 IEC 61009-1 BS EN 61009-1 IEC 61009-2-2
Ip Degree Of Protection	IP20
Tropicalisation	2
Relative Humidity	95 % at 55 °C
Ambient Air Temperature For Operation	-1560 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.3 cm
Package 1 Width	1.8 cm
Package 1 Length	11.03 cm
Package 1 Weight	207 g

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations Circularity Profile