Product datasheet

Specification





TeSys D contactor 3P 65A AC-3 up to 440V coil 24-60V AC/DC ring-lugs

LC1D65A6BNE

EAN Code: 3606489493417

Main

Range	TeSys	
Nange	·	
	TeSys Deca	
Range Of Product	TeSys Deca	
But divided On On the state of Table		
Product Or Component Type	Contactor	
Device Short Name	LC1D	
Contactor Application	Motor control	
	Resistive load	
Utilisation Category	AC-3	
	AC-1	
	AC-3e	
Poles Description	3P	
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz	
[le] Rated Operational Current	80 A (at <60 °C) at <= 440 V AC-1 for power circuit	
	65 A (at <60 °C) at <= 440 V AC-3 for power circuit	
	65 A (at <60 °C) at <= 440 V AC-3e for power circuit	
[Uc] Control Circuit Voltage	2460 V AC 50/60 Hz	
	2460 V DC	

Complementary

Motor Power Kw	18.5 kW at 220230 V AC 50 Hz (AC-3)
	30 kW at 380400 V AC 50 Hz (AC-3)
	37 kW at 415 V AC 50 Hz (AC-3)
	37 kW at 440 V AC 50 Hz (AC-3)
	37 kW at 500 V AC 50 Hz (AC-3)
	37 kW at 660690 V AC 50 Hz (AC-3)
	18.5 kW at 220230 V AC 50 Hz (AC-3e)
	30 kW at 380400 V AC 50 Hz (AC-3e)
	37 kW at 415 V AC 50 Hz (AC-3e)
	37 kW at 440 V AC 50 Hz (AC-3e)
	37 kW at 500 V AC 50 Hz (AC-3e)
	37 kW at 660690 V AC 50 Hz (AC-3e)
Motor Power Hp	5 hp at 115 V AC 60 Hz for 1 phase motors
	10 hp at 230/240 V AC 60 Hz for 1 phase motors
	20 hp at 200/208 V AC 60 Hz for 3 phases motors
	20 hp at 230/240 V AC 60 Hz for 3 phases motors
	40 hp at 460/480 V AC 60 Hz for 3 phases motors
	50 hp at 575/600 V AC 60 Hz for 3 phases motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With
[Ith] Conventional Free Air Thermal Current	80 A (at 60 °C) for power circuit
merma ourrent	10 A (at 60 °C) for signalling circuit

Irms Rated Making Capacity	1000 A at 440 V for power circuit conforming to IEC 60947
	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1
Rated Breaking Capacity	1000 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand	110 A 40 °C - 10 min for power circuit
Current	260 A 40 °C - 1 min for power circuit
	640 A 40 °C - 10 s for power circuit
	900 A 40 °C - 1 s for power circuit 100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	125 A gG at <= 690 V coordination type 1 for power circuit
	125 A gG at <= 690 V coordination type 2 for power circuit
	10 A gG for signalling circuit conforming to IEC 60947-5-1
Average Impedance	1.5 mOhm - Ith 80 A 50 Hz for power circuit
Power Dissipation Per Pole	9.6 W AC-1
	6.3 W AC-3 6.3 W AC-3e
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1
of Nated Histiation Voltage	Signalling circuit: 690 V conforming to IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand /oltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1
	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
lechanical Durability	6 Mcycles
Electrical Durability	1.8 Mcycles 57 A AC-3 at Ue <= 440 V
	0.5 Mcycles 80 A AC-1 at Ue <= 440 V 1.8 Mcycles 57 A AC-3e at Ue <= 440 V
Control Circuit Type	AC/DC at 50/60 Hz AC/DC electronic
Coil Technology	Built-in bidirectional peak limiting
Control Circuit Voltage Limits	<= 0.1 Uc (-4070 °C):drop-out AC/DC
	0.851.1 Uc (-4060 °C):operational AC
	0.81.1 Uc (-4060 °C):operational DC 11.1 Uc (6070 °C):operational AC/DC
nrush Power In Va	15 VA 50/60 Hz (at 20 °C)
nrush Power In W	16 W (at 20 °C)
Hold-In Power Consumption In Va	1 VA 50/60 Hz (at 20 °C)
Hold-In Power Consumption In W	0.7 W at 20 °C
Heat Dissipation	0.7 W at 20 °C 0.7 W at 50/60 Hz
·	
Operating Time	5565 ms closing 2080 ms opening
Maximum Operating Rate	3600 cyc/h 60 °C
Connections - Terminals	Power circuit: lugs-ring terminals - external diameter: 16.5 mm Control circuit: lugs-ring terminals - external diameter: 8 mm
Tightening Torque	Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver flat Ø 6 mm M3.5
	Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver Philips No 2 M3.5
	Power circuit: 6 N.m - on lugs-ring terminals hexagonal screw head 10 mm M6
	Power circuit: 6 N.m - on lugs-ring terminals - with screwdriver pozidriv No 2 M4
	Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver pozidriv No 2 M3.5
Auxiliary Contact Composition	1 NO + 1 NC
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1
	type mirror contact 1 NC conforming to IEC 60947-4-1

Signalling Circuit Frequency	25400 Hz	
Minimum Switching Voltage	17 V for signalling circuit	
Minimum Switching Current	5 mA for signalling circuit	
Insulation Resistance	> 10 MOhm for signalling circuit	
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact	
Mounting Support	Rail Plate	

Environment

Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 IEC 60335-1
Product Certifications	CCC CSA EAC UL KC DNV-GL LROS (Lloyds register of shipping) UKCA
Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Climatic Withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating
Operating Altitude	03000 m
Fire Resistance	850 °C conforming to IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor open (10 Gn for 11 ms) Shocks contactor closed (15 Gn for 11 ms)
Height	122 mm
Width	55 mm
Depth	120 mm
Net Weight	1.002 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	13.7 cm
Package 1 Length	15.2 cm
Package 1 Weight	905.0 g

Contractual warranty

Warranty	18 months

Sustainability Green Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information