



Acti9 Isobar B - pan assembly - 8 ways TP + earth + neutral

SEA9BN8E

Local distributor code: 396792860

! Discontinued on: 7 Feb 2024

EAN Code: 5018934962870

Main

Range	Acti9
Product Or Component Type	Pan assembly
Device Application	Distribution

Complementary

Range Compatibility	Acti 9 Acti9 Isobar B distribution board
Incomer Device Options	4P switch disconnector
	4P terminal block
	3P + N RCCB
	3P + N MCCB
	4P contactor
Protection Device Options At Outgoer	Residual current circuit breaker with overcurrent protection (RCBO) 45 A max Miniature circuit breaker (MCB) 63 A max
Number Of Ways	8 ways - 3P + N + E
Busbar Pitch	18 mm
Length	471 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.6 cm
Package 1 Width	38.6 cm
Package 1 Length	49.0 cm
Package 1 Weight	4.19 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	48
Package 2 Height	112.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	233.68 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø

Rohs Exemption Information

Yes



Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations