

# Product data sheet

Specifications



## Switch disconnector fuse, TeSys GS, 4P, 100A, fuse type BS, size A4

GS2JB4

### Main

Range	TeSys
Product Name	TeSys GS
Device Short Name	GS2J
Product Or Component Type	Switch-disconnector-fuse
Poles Description	4P
Protected Poles Description	4t
Contacts Type And Composition	4 NO
[Ith] Conventional Free Air Thermal Current	100 A (at 40 °C)
[Ie] Rated Operational Current	100 A at 440 V 2 poles in series per phase DC-23A 100 A at 440 V 2 poles in series per phase DC-23B 100 A at 690 V poles not juxtaposed AC-23A 100 A at 690 V poles not juxtaposed AC-23B 100 A at 400 V AC-23A 100 A at 400 V AC-23B 100 A at 500 V AC-23A 100 A at 500 V AC-23B
Fuse Type	BS
Fuse Size	A4
Network Type	AC DC
Network Frequency	50/60 Hz

### Complementary

Type Of Operating Handle	External right side External frontal
Mounting Support	Plate
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
Rated Operational Power In W	51 kW at 400 V 63 kW at 500 V 90 kW at 690 V
Making Capacity	1000 A at 400 V AC-23B
Breaking Capacity	800 A at 400 V (AC-23B)
Short-Circuit Withstand	20 kA
Mechanical Durability	10000 cycles

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical Durability	1500 cycles AC-23A 1500 cycles AC-23B 300 cycles AC-23A 300 cycles AC-23B
Connections - Terminals	Power circuit: bars20 mm <sup>2</sup> Power circuit: lugs-ring terminals25...95 mm <sup>2</sup>
[Icm] Rated Short-Circuit Making Capacity	80 kA at 400 V with protection by gG fuses
Tightening Torque	Power circuit: 12 N.m

## Environment

Standards	IEC 60947-3
Product Certifications	CE
Ip Degree Of Protection	IP20 conforming to IEC 60529 (with terminal cover)
Ambient Air Temperature For Operation	-20...70 °C
Ambient Air Temperature For Storage	-40...80 °C
Fire Resistance	850 °C fuse cover conforming to IEC 60695-2-1 960 °C body conforming to IEC 60695-2-1
Height	162 mm
Width	184 mm
Depth	116 mm
Net Weight	2 kg

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	17.0 cm
Package 1 Length	21.0 cm
Package 1 Weight	2.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to <a href="#">www.P65Warnings.ca.gov</a>