

Product data sheet

Specifications



Switch disconnector fuse, TeSys GS, 3P, 160A, fuse type DIN, size 0

GS2L3

Main

Range	TeSys
Product Name	TeSys GS
Device Short Name	GS2L
Product Or Component Type	Switch-disconnector-fuse
Poles Description	3P
Protected Poles Description	3t
Contacts Type And Composition	3 NO
[Ith] Conventional Free Air Thermal Current	160 A (at 40 °C)
[Ie] Rated Operational Current	125 A at 440 V 2 poles in series per phase DC-23A 125 A at 440 V 2 poles in series per phase DC-23B 125 A at 690 V AC-23A 125 A at 690 V AC-23B 160 A at 400 V AC-23A 160 A at 400 V AC-23B 160 A at 500 V AC-23A 160 A at 500 V AC-23B
Fuse Type	DIN
Fuse Size	0
Network Type	DC AC
Network Frequency	50/60 Hz

Complementary

Type Of Operating Handle	External right side External frontal
Mounting Support	Plate
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
Rated Operational Power In W	80 kW at 400 V 110 kW at 500 V 110 kW at 690 V
Making Capacity	1600 A at 400 V AC-23B
Breaking Capacity	1280 A at 400 V (AC-23B)
Short-Circuit Withstand	20 kA
Mechanical Durability	10000 cycles

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical Durability	1000 cycles AC-23A 1000 cycles AC-23B 200 cycles DC-23A 200 cycles DC-23B
Connections - Terminals	Power circuit: bars20 mm² Power circuit: lugs-ring terminals50...95 mm²
[Icm] Rated Short-Circuit Making Capacity	100 kA at 400 V with protection by gG fuses
Tightening Torque	Power circuit: 12 N.m

Environment

Standards	IEC 60947-3
Product Certifications	CE
Ip Degree Of Protection	IP20 conforming to IEC 60529 (with terminal cover)
Ambient Air Temperature For Operation	-20...70 °C
Ambient Air Temperature For Storage	-40...80 °C
Fire Resistance	850 °C fuse cover conforming to IEC 60695-2-1 960 °C body conforming to IEC 60695-2-1
Height	162 mm
Width	190 mm
Depth	136.5 mm
Net Weight	1.8 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.0 cm
Package 1 Width	21.0 cm
Package 1 Length	26.0 cm
Package 1 Weight	2.318 kg
Unit Type Of Package 2	S06
Number Of Units In Package 2	24
Package 2 Height	75.0 cm
Package 2 Width	60.0 cm
Package 2 Length	80.0 cm
Package 2 Weight	68.632 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov