## **Product datasheet**

Specification





# logic controller, Modicon M221, 40 IO, transistor, PNP

TM221C40T

#### Main

Range Of Product	Modicon M221	
Product Or Component Type	Logic controller	
[Us] Rated Supply Voltage	24 V DC	
Discrete Input Number	24, discrete input 4 fast input conforming to IEC 61131-2 Type 1	
Analogue Input Number	2 at 010 V	
Discrete Output Type	Transistor	
Discrete Output Number	16 transistor 2 fast output	
Discrete Output Voltage	24 V DC	
Discrete Output Current	0.5 A	

## Complementary

oompicinental y		
Discrete I/O Number	40	
Maximum Number Of I/O Expansion Module	7 (local I/O-Architecture) 14 (remote I/O-Architecture)	
Supply Voltage Limits	20.428.8 V	
Inrush Current	35 A	
Maximum Power Consumption In W	4.1 W at 24 V (without I/O expansion module) 16 W at 24 V (with max number of I/O expansion module)	
Power Supply Output Current	0.52 A 5 V for expansion bus 0.3 A 24 V for expansion bus	
Discrete Input Logic	Sink or source (positive/negative)	
Discrete Input Voltage	24 V	
Discrete Input Voltage Type	DC	
Analogue Input Resolution	10 bits	
Lsb Value	10 mV	
Conversion Time	1 ms per channel + 1 controller cycle time for analogue input analog input	
Permitted Overload On Inputs	+/- 30 V DC for 5 min (maximum) for analog input +/- 13 V DC (permanent) for analog input	
Voltage State 1 Guaranteed	>= 15 V for input	
Voltage State 0 Guaranteed	<= 5 V for input	
Discrete Input Current	7 mA for discrete input 5 mA for fast input	
Input Impedance	Impedance 3.4 kOhm for discrete input 100 kOhm for analog input 4.9 kOhm for fast input	

Response Time	35 μs turn-off, 1215 terminal(s) for input 5 μs turn-on, 10, 11, 16, 17 terminal(s) for fast input 35 μs turn-on, other terminals terminal(s) for input 5 μs turn-off, 10, 11, 16, 17 terminal(s) for fast input 100 μs turn-off, other terminals terminal(s) for input 5 μs turn-on, turn-off, Q0Q1 terminal(s) for output 50 μs turn-on, turn-off, Q2Q3 terminal(s) for output 300 μs turn-on, turn-off, other terminals terminal(s) for output	
Configurable Filtering Time	0 ms for input 3 ms for input 12 ms for input	
Discrete Output Logic	Positive logic (source)	
Maximum Current Per Output Common	4 A	
Output Frequency	100 kHz for fast output (PWM/PLS mode) at Q0Q1 5 kHz for output at Q2Q3 0.1 kHz for output at Q4Q15	
Absolute Accuracy Error	+/- 1 % of full scale for analog input	
Maximum Leakage Current	0.1 mA for transistor output	
Maximum Voltage Drop	<1 V	
Mechanical Durability	20000000 cycles for transistor output	
Maximum Tungsten Load	<12 W for output and fast output	
Protection Type	Overload and short-circuit protection at 1 A	
Reset Time	1 s automatic reset	
Memory Capacity	256 kB for user application and data RAM with 10000 instructions 256 kB for internal variables RAM	
Data Backed Up	256 kB built-in flash memory for backup of application and data	
Data Storage Equipment	2 GB SD card (optional)	
Battery Type	BR2032 or CR2032X lithium non-rechargeable	
Backup Time	1 year at 25 °C (by interruption of power supply)	
Execution Time For 1 Kinstruction	0.3 ms for event and periodic task	
Execution Time Per Instruction	0.2 μs Boolean	
Exct Time For Event Task	60 μs response time	
Maximum Size Of Object Areas	255 %TM timers 512 %M memory bits 255 %C counters 512 %KW constant words 8000 %MW memory words	
Realtime Clock	With	
Clock Drift	<= 30 s/month at 25 °C	
Regulation Loop	Adjustable PID regulator up to 14 simultaneous loops	
Positioning Functions	Position PTO 2 axe(s)pulse/direction mode (100 kHz) Position PTO 1 axe(s)CW/CCW mode (100 kHz)	
Function Available	Frequency generator PWM PLS	
Counting Input Number	4 fast input (HSC mode) at 100 kHz 32 bits	
Counter Function	Pulse/direction Single phase A/B	
Integrated Connection Type	USB port with mini B USB 2.0 connector  Non isolated serial link serial 1 with RJ45 connector and RS485 interface  Non isolated serial link serial 2 with RJ45 connector and RS232/RS485 interface	

Supply (serial)serial link supply: 5 V, <200 mA		
Transmission Rate	1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232 480 Mbit/s for USB	
Communication Port Protocol	USB port: USB - SoMachine-Network Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network	
Local Signalling	1 LED (green) for PWR 1 LED (green) for RUN 1 LED (red) for module error (ERR) 1 LED (green) for SD card access (SD) 1 LED (red) for BAT 1 LED (green) for SL1 1 LED (green) for SL2 1 LED per channel (green) for I/O state	
Electrical Connection	removable screw terminal block for inputs removable screw terminal block for outputs terminal block, 3 terminal(s) for connecting the 24 V DC power supply connector, 4 terminal(s) for analogue inputs Mini B USB 2.0 connector for a programming terminal	
Maximum Cable Distance Between Devices	Shielded cable: <10 m for fast input Unshielded cable: <30 m for output Unshielded cable: <30 m for digital input Unshielded cable: <1 m for analog input Shielded cable: <3 m for fast output	
Insulation	Between input and internal logic at 500 V AC Between fast input and internal logic at 500 V AC Non-insulated between inputs Between output and internal logic at 500 V AC Non-insulated between analogue input and internal logic Non-insulated between analogue inputs	
Marking	CE	
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 plate or panel with fixing kit	
Height	90 mm	
Depth	70 mm	
Width	160 mm	
Net Weight	0.456 kg	
Environment		
Standards	IEC 61131-2 UL 508 CAN/CSA C22.2 No. 213 IACS E10 ANSI/ISA 12-12-01	
Product Certifications  DNV-GL  ABS  EAC  cULus  RCM		

Standards	IEC 61131-2 UL 508 CAN/CSA C22.2 No. 213 IACS E10 ANSI/ISA 12-12-01	
Product Certifications	DNV-GL ABS EAC cULus RCM LR CE UKCA cULus HazLoc	
Environmental Characteristic	Ordinary and hazardous location	
Resistance To Electrostatic Discharge	8 kV in air conforming to IEC 61000-4-2 4 kV on contact conforming to IEC 61000-4-2	
Resistance To Electromagnetic Fields	10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3 3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3 1 V/m 22.7 GHz conforming to IEC 61000-4-3	
Resistance To Magnetic Fields	30 A/m 50/60 Hz conforming to IEC 61000-4-8	

Resistance To Fast Transients	2 kV (power lines) conforming to IEC 61000-4-4	
	2 kV (relay output) conforming to IEC 61000-4-4	
	1 kV (I/O) conforming to IEC 61000-4-4	
	1 kV (Ethernet line) conforming to IEC 61000-4-4 1 kV (serial link) conforming to IEC 61000-4-4	
Surge Withstand	2 kV power lines (AC) common mode conforming to IEC 61000-4-5	
· ·	2 kV relay output common mode conforming to IEC 61000-4-5	
	1 kV I/O common mode conforming to IEC 61000-4-5	
	1 kV shielded cable common mode conforming to IEC 61000-4-5	
	0.5 kV power lines (DC) differential mode conforming to IEC 61000-4-5	
	1 kV power lines (AC) differential mode conforming to IEC 61000-4-5	
	1 kV relay output differential mode conforming to IEC 61000-4-5 0.5 kV power lines (DC) common mode conforming to IEC 61000-4-5	
Resistance To Conducted	10 V 0.1580 MHz conforming to IEC 61000-4-6	
Disturbances	3 V 0.180 MHz conforming to field 6 1000-4-0	
	10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to	
	Marine specification (LR, ABS, DNV, GL)	
Electromagnetic Emission	Conducted emissions - test level: 79 dBµV/m QP/66 dBµV/m AV ( power lines (AC))	
	at 0.150.5 MHz conforming to IEC 55011	
	Conducted emissions - test level: 73 dBμV/m QP/60 dBμV/m AV ( power lines (AC))	
	at 0.5300 MHz conforming to IEC 55011	
	Conducted emissions - test level: 12069 dBµV/m QP ( power lines) at 10150 kHz	
	conforming to IEC 55011	
	Conducted emissions - test level: 63 dBµV/m QP ( power lines) at 1.530 MHz	
	conforming to IEC 55011  Radiated emissions - test level: 40 dBµV/m QP class A ( 10 m) at 30230 MHz	
	conforming to IEC 55011	
	Conducted emissions - test level: 7963 dBµV/m QP ( power lines) at 1501500	
	kHz conforming to IEC 55011	
	Radiated emissions - test level: 47 dBµV/m QP class A ( 10 m) at 2001000 MHz	
	conforming to IEC 55011	
Immunity To Microbreaks	10 ms	
Ambient Air Temperature For Operation	-1055 °C (horizontal installation) -1035 °C (vertical installation)	
Ambient Air Temperature For Storage	-2570 °C	
Relative Humidity	1095 %, without condensation (in operation)	
•	1095 %, without condensation (in storage)	
Ip Degree Of Protection	IP20 with protective cover in place	
Pollution Degree	<= 2	
Operating Altitude	02000 m	
Storage Altitude		
	03000 m	
Vibration Resistance	3.5 mm at 58.4 Hz on symmetrical rail	
	3.5 mm at 58.4 Hz on panel mounting	
	1 gn at 8.4150 Hz on symmetrical rail	
	1 gn at 8.4150 Hz on panel mounting	
Shock Resistance	147 m/s² for 11 ms	
Packing Units		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	11.172 cm	

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.172 cm
Package 1 Width	14.117 cm
Package 1 Length	21.084 cm
Package 1 Weight	750.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	12

Package 2 Height	29.2 cm
Package 2 Width	39.6 cm
Package 2 Length	56.8 cm
Package 2 Weight	10.101 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	144
Package 3 Height	105.0 cm
Package 3 Width	120.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	135 kg



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
	Pvc Free	

#### **Certifications & Standards**


Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
<b>Environmental Disclosure</b>	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	


## **Product datasheet**

## TM221C40T

## **Dimensions Drawings**

#### **Dimensions**







## TM221C40T

Mounting and Clearance

Mounting on a Rail





#### **Direct Mounting on a Panel Surface**



(1) Install a mounting strip


#### **Mounting Hole Layout**






#### **Mounting**

#### **Correct Mounting Position**




#### **Acceptable Mounting Position**




#### **Incorrect Mounting Position**









#### Clearance





#### Connections and Schema

#### **Digital Inputs**




- (\*) Type T fuse
- (A) Sink wiring (positive logic).
- (B) Source wiring (negative logic).

#### **Connection of the Fast Inputs**




10, 11, 16, 17

#### **Transistor Outputs**




- (\*) Type T fuse
- (1) The V0+ and V1+ terminals are **not** connected internally.
- (2) The V0- and V1- terminals are **not** connected internally.


#### **Connection of the Fast Outputs**



Q0, Q1

#### **Analog Inputs**






The (-) poles are connected internally.


Pin	Wire Color
0 V	Black
AN1	Red
0 V	Black
AN0	Red

#### **USB Mini-B Connection**



15

#### **SL1 Connection**




SL1


Ν°	RS 232	RS 485
1	RxD	N.C.
2	TxD	N.C.
3	RTS	N.C.
4	N.C.	D1
5	N.C.	D0
6	стѕ	N.C.
7	N.C*.	5 Vdc
8	Common	Common

N.C.: not connected

 $<sup>\</sup>ensuremath{^*}$  : 5 Vdc delivered by the controller. Do not connect.



#### **SL2 Connection**




Ν°	RS 485
1	N.C.
2	N.C.
3	N.C.
4	D1
5	D0
6	N.C.
7	N.C.
8	Common

N.C.: not connected

#### Performance Curves

#### **Derating Curves**


#### **Embedded Digital Inputs (No Cartridge)**



X: Ambient temperature

Y: Input simultaneous ON ratio

## **Embedded Digital Inputs (with Cartridge)**




X: Ambient temperature

Y: Input simultaneous ON ratio

#### **Derating Curves**


#### **Embedded Digital Outputs (No Cartridge)**



Ambient temperature

Output simultaneous ON ratio

#### **Embedded Digital Outputs (with Cartridge)**



X: Ambient temperature

Output simultaneous ON ratio