Specifications





# controller, Modicon Easy M200, 40 IO, relay, Ethernet

TM200CE40R

## Main

Range Of Product	Easy Modicon M200
Product Or Component Type	Logic controller
[Us] Rated Supply Voltage	100240 V AC
Discrete I/O Number	40
Discrete Input Number	I2I5: 4 fast input I0, I1, I6, I7: 4 high speed input I8I23: 16 regular input
Discrete Output Number	16 relay
Discrete Input Voltage	24 V
Discrete Input Voltage Type	DC
Discrete Input Current	7 mA for input
Discrete Input Logic	Sink or source (positive/negative) type 1 conforming to IEC 61131-2
Discrete Output Voltage	24 V DC 220 V AC
Discrete Output Current	2 A
Discrete Output Type	Relay normally open
Power Consumption In Va	5969 VA at 100240 V AC (with max I/O)

## Complementary

Maximum Number Of I/O Expansion Module	4 with 128 discrete output(s) for transistor output 4 with 80 discrete output(s) for relay output	
Supply Voltage Limits	85264 V	
Network Frequency	50/60 Hz	
Inrush Current	50 A	
Voltage State 1 Guaranteed	>= 15 V for input	
Voltage State 0 Guaranteed	<= 5 V for input	
Input Impedance	3.3 kOhm for discrete input	
Response Time	5 μs turn-off, I0, I1, I6, I7 terminal(s) for high speed input 5 μs turn-on, I0, I1, I6, I7 terminal(s) for high speed input 100 μs turn-off, I2I5 terminal(s) for fast input 35 μs turn-on, I2I5 terminal(s) for fast input 100 μs turn-off, I8I13 terminal(s) for regular input 35 μs turn-on, I8I13 terminal(s) for regular input 10 ms turn-off, Q0Q15 terminal(s) for relay output 10 ms turn-off, I14I23 terminal(s) for regular input 55 μs turn-on, I14I23 terminal(s) for regular input	

Configurable Filtering Time	0 ms for input 3 ms for input 12 ms for input	
Output Voltage Limits	30 V DC 250 V AC	
Maximum Current Per Output Common	4 A	
Electrical Durability	100000 cycles AC-12, 240 V, 480 VA, resistive 100000 cycles DC-12, 24 V, 48 W, resistive	
Switching Frequency	0.1 Hz with maximum load	
Mechanical Durability	2000000 cycles for relay output	
Minimum Load	10 mA at 5 V DC for relay output	
Memory Capacity	512 byte internal flash for backup of programs	
Data Storage Equipment	32 GB micro SD card (optional)	
Battery Type	BR2032 Li-CFx (Lithium-Carbon Monofluoride), battery life: 5 year(s)	
Backup Time	3 years at 25 °C (by interruption of power supply)	
Execution Time For 1 Kinstruction	0.3 ms for event and periodic task	
Execution Time Per Instruction	0.2 µs Boolean	
Exct Time For Event Task	60 µs response time	
Clock Drift	<= 90 s/month at 25 °C	
Regulation Loop	Adjustable PID regulator up to 14 simultaneous loops	
Control Signal Type	Quadrature (x1, x2, x4) at 100 kHz for fast input (HSC mode) Pulse/direction at 100 kHz for fast input (HSC mode) Single phase at 100 kHz for fast input (HSC mode) CW/CCW at 100 kHz for fast input (HSC mode)	
Counting Input Number	4 fast input (HSC mode) at 100 kHz 32 bits	
Integrated Connection Type	USB port with mini B USB 2.0 connector Non isolated serial link serial 1 with terminal block connector and RS485 interface Non isolated serial link serial 2 with terminal block connector and RS232/RS485 interface Ethernet Modbus TCP/IP Ethernet with RJ45 connector and 1 Ethernet port 10/100BASE-T interface Isolated serial link serial 2 with terminal block connector and RS485 interface	
Transmission Rate	<ul> <li>1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485</li> <li>1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232</li> <li>12 Mbit/s for USB</li> <li>10/100 Mbit/s for bus length of 100 m for Ethernet Modbus TCP/IP</li> </ul>	
Communication Port Protocol	USB port: USB - SoMachine-Network Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network Ethernet Modbus TCP/IP: Modbus TCP/IP client/server	
Local Signalling	1 LED (green) for PWR 1 LED (green) for RUN 1 LED (red) for module error (ERR) 1 LED (green) for SD card access (SD) 1 LED (red) for BAT 1 LED (green) for SL1 1 LED per channel (green) for I/O state 2 LEDs (green) for communication (LK/ACT 10/100)	
Electrical Connection	Mini B USB 2.0 connectorfor a programming terminal RJ45 connectorfor connecting Ethernet network removable screw terminal blockfor inputs removable screw terminal blockfor outputs removable screw terminal block, 4 terminal(s) for connecting the serial link1 removable screw terminal block, 3 terminal(s) for connecting the 100-240 V AC power supply	

Maximum Cable Distance Between Devices	Unshielded cable: <50 m for input Shielded cable: <10 m for fast input Shielded cable: <10 m for high speed input Unshielded cable: <150 m for output	
Insulation	Non-insulated between inputs Between output and internal logic at 1780 V AC Between output groups at 1780 V AC Between supply and internal logic at 1780 V AC Between input and internal logic at 500 V AC Between fast input and internal logic at 500 V AC Between input groups at 500 V AC	
Sensor Power Supply	24 V DC at 300 mA supplied by the controller	
Marking	CE	
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 plate or panel with fixing kit conforming to IEC 60715	
Height	90 mm	
Depth	70 mm	
Width	175 mm	
Net Weight	0.512 kg	

## Environment

Ip Degree Of Protection	IP20 with protective cover in place
Product Certifications	RCM IACS E10 CSA cULus
Standards	IEC 61010-2-201 IEC 61131-2

Electromagnetic Compatibility	Electrostatic discharge immunity test - test level: 8 kV (air discharge) conforming to IEC 61000-4-2
	Electrostatic discharge immunity test - test level: 6 kV (contact discharge) conforming to IEC 61000-4-2
	Susceptibility to electromagnetic fields - test level: 10 V/m (80 MHz3 GHz) conforming to IEC 61000-4-3
	Magnetic field at power frequency - test level: 30 A/m conforming to IEC 61000-4-8 Electrical fast transient/burst immunity test - test level: 2 kV (power lines) conforming to IEC 61000-4-4
	Electrical fast transient/burst immunity test - test level: 2 kV (relay output) conforming to IEC 61000-4-4
	Electrical fast transient/burst immunity test - test level: 1 kV (I/O) conforming to IEC 61000-4-4
	Electrical fast transient/burst immunity test - test level: 1 kV (serial link) conforming to IEC 61000-4-4
	1.2/50 µs shock waves immunity test - test level: 1 kV (power lines (DC)) conforming to IEC 61000-4-5
	1.2/50 µs shock waves immunity test - test level: 2 kV (power lines (AC)) conforming to IEC 61000-4-5
	1.2/50 µs shock waves immunity test - test level: 2 kV (relay output) conforming to IEC 61000-4-5
	1.2/50 µs shock waves immunity test - test level: 1 kV (I/O) conforming to IEC 61000-4-5
	1.2/50 µs shock waves immunity test - test level: 1 kV (shielded cable) conforming to IEC 61000-4-5
	1.2/50 µs shock waves immunity test - test level: 0.5 kV (power lines (DC)) conforming to IEC 61000-4-5
	1.2/50 $\mu s$ shock waves immunity test - test level: 1 kV (power lines (AC)) conforming to IEC 61000-4-5
	Conducted RF disturbances - test level: 10 V (0.1580 MHz) conforming to IEC 61000-4-6
	Conducted emission - test level: 79 dBµV/m QP/66 dBµV/m AV (power lines (AC)) conforming to IEC 55011
	Conducted emission - test level: 73 dBµV/m QP/60 dBµV/m AV (power lines (AC)) conforming to IEC 55011
	Radiated emission - test level: 40 dB $\mu$ V/m QP class A (10 m) conforming to IEC 55011
	Radiated emission - test level: 47 dB $\mu$ V/m QP class A (10 m) conforming to IEC 55011
	Electrical fast transient/burst immunity test - test level: 1 kV (Ethernet line) conforming to IEC 61000-4-4
Shock Resistance	15 gn for 11 ms 30 gn for 6 ms
Immunity To Microbreaks	10 ms
Vibration Resistance	3.5 mm at 5…8.4 Hz on symmetrical rail 1 gn at 8.4…150 Hz on symmetrical rail
	3.5 mm at 58.7 Hz on panel mounting 2 gn at 8.7150 Hz on panel mounting
Relative Humidity	1095 %, without condensation (in operation) 1095 %, without condensation (in storage)
Ambient Air Temperature For Operation	055 °C (horizontal installation)
Ambient Air Temperature For Storage	-2570 °C
Pollution Degree	<= 2
Operating Altitude	02000 m
Storage Altitude	03000 m

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.498 cm
Package 1 Width	13.66 cm
Package 1 Length	18.72 cm
Package 1 Weight	771 g

Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	9773 g
Unit Type Of Package 3	P12
Number Of Units In Package 3	288
Package 3 Height	95 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	243552 g

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Mercury Free

Rohs Exemption Information


## **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	

**Dimensions Drawings** 

## **Dimensions Drawings**


#### Dimensions




Mounting and Clearance

Mounting and Clearance


### Mounting on a Rail




#### **Direct Mounting on a Panel Surface**




**Mounting Position** 














Clearance





#### TMCR2---Installation















TMCR2 ··· De-Installation








## TM200CE40R



Connections and Schema


## Wiring Diagram / Connections Schema

#### **AC Power Supply**



(\*) Type T fuse

#### **Digital Inputs Positive Logic (Sink)**




(\*) Type T fuse

(\*\*) Fast inputs

(1) The COM0 and COM1 terminals are not connected internally.

#### **Digital Inputs Negative Logic (Source)**





(\*) Type T fuse


(\*\*) Fast inputs

(1) The COM0 and COM1 terminals are not connected internally.

#### Relay Outputs - Negative Logic (Sink)








(\*) Type T fuse

(1) The COM0 and COM1 terminals are not connected internally.

(2) A free wheeling diode or an RC snubber

#### Relay Outputs - Positive Logic (Source)




(\*) Type T fuse

(1) The COM0 and COM1 terminals are not connected internally.

(2) A free wheeling diode or an RC snubber


#### **Ethernet Connection**




Pin N°	Signal
1	TD +
2	TD —
3	RD+
4	_
5	_
6	RD —

Pin N°	Signal
7	-
8	_

#### **USB Mini-B Connection**



#### **SL1** Connection




D1 : D1 (A+) D0 : D0 (B-) Shield : Shield COM : O V Com

Performance Curves

### **Derating Curves**

#### **Relay Outputs**



 $\boldsymbol{X}$  : Ambient temperature (°C / °F)

Y: Output load current (%)